


Multilayer Chip Band Pass Filters For 2.4GHz W-LAN/Bluetooth


Conformity to RoHS Directive

DEA Series DEA162450BT-2181D1

SHAPES AND DIMENSIONS



RECOMMENDED PC BOARD PATTERNS



ELECTRICAL CHARACTERISTICS

Item			Typical value
Frequency range(Pass band)	2400 to 2500MHz		—
Insertion loss	[2400 to 2500MHz]	2.2dB max.	1.78dB
VSWR	[2400 to 2500MHz]	1.92 max.	1.10
Attenuation	[880 to 915MHz]	35dB min.	40.6dB
	[1710 to 1850MHz]	32dB min.	41.2dB
	[1850 to 1910MHz]	32dB min.	36.1dB
	[1920 to 1990MHz]	28dB min.	31.2dB
	[2110 to 2170MHz]	25dB min.	27.1dB
	[4800 to 5000MHz]	30dB min.	40.5dB
Temperature range	[7200 to 7500MHz]	25dB min.	34.1dB
	Operating	-40 to +85°C	
	Storage	-40 to +85°C	


• Ta:+25°C

• Conformity to RoHS Directive: This means that, in conformity with EU Directive 2002/95/EC, lead, cadmium, mercury, hexavalent chromium, and specific bromine-based flame retardants, PBB and PBDE, have not been used, except for exempted applications.


• All specifications are subject to change without notice.

FREQUENCY CHARACTERISTICS


INSERTION LOSS




ATTENUATION



RETURN LOSS



VSWR



• All specifications are subject to change without notice.