

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

08-65-0815

Status:


Active

Overview:

KK® 396 RPC Connector System

Description:

KK® Crimp Terminal 6459, 22-30 AWG, Reel, Phosphor Bronze Selective Gold (Au)



Documents:

Drawing (PDF)

Product Specification PS-10-07 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	6459
Application	Signal
Crimp Quality Equipment	Yes
Overview	KK® 396 RPC Connector System
Packaging Alternative	08-65-0816 (Loose)
Product Name	KK®
UPC	800754227421
Physical	
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Net Weight	0.069/g
Packaging Type	Reel
Plating min - Mating	0.381µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.57mm max.
Wire Size AWG	22, 24, 26, 28, 30
Wire Size mm²	N/A
Material Info	
Old Part Number	6459-(555)
Reference - Drawing Numbers	
Product Specification	PS-10-07
Sales Drawing	SD-6459

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

6459Series

Use With

2.54mm Pitch KK® Crimp Terminal Housing 2695

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Mini-Mac™	0011182171
Applicator	
Extraction Tool	0011030022
Terminator Die	0011402265
Insertion Tool	0638120000
Mini-Mac™	0638882000
Applicator, Use with Large Wire Insulation Diameter	

Mini-Mac™	<u>0638882100</u>
Applicator, Use with	
Small Wire Insulation	
Diameter	

This document was generated on 08/28/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION