



REVISIONS

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1891	A	RELEASED	EO	06/27/06	SA	7/25/06	HO	7/25/06



RoHS
Compliant



SPECIFICATION:

1. Product Description
Bare Copper Solid, Polypropylene Insulated,
Four-Conductor Cable
Flame Retardant PVC Jacket.

2. Insulation:

Conductor	Insulation	
AWG	Material	O.D.
24(1/0.5mm)	PP	0.95±0.05mm

3. Jacket:

Material	O.D.	Color
FR-PVC	4.0±0.1mm	Beige

4. Electrical & Physical Properties:

- UL & CSA Style
- Temperature & Voltage Rating: 60°C – 30 V
- Conductor Resistance: 93 Ohm/KM Max. at 20°C
- Insulation Resistance: 100 Megohm/KM Min. at 20°C
- Dielectric Strength: 500 VAC/1 Min.
- Spark Test: 2 KV in Air

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:

Unless Otherwise Specified
.X ±0.2 [0.008]
.XX ±0.12 [0.005]

DRAWN BY:	DATE:
EKLAS ODISH	06/27/06
CHECKED BY:	DATE:
SAMI ALNADI	7/25/06
APPROVED BY:	DATE:
HISHAM ODISH	7/25/06

DRAWING TITLE:

Round Telephone Cable, 24 AWG, 4 Solid Conductors, Knockout Box

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	SPC19782	84K8546.DWG	A
SCALE: NTS		U.O.M.: mm [INCHES]	SHEET: 1 OF 1