

Wire-wound Chip Power Inductors (CB series)

CBC2012T220M



■ Features

- Item Summary
22 μ H($\pm 20\%$), 170mA, 190mA, 0805
- Lifecycle Stage
Mass Production
- Standard packaging quantity (minimum)
Taping 3000pcs

■ Products characteristics table

CaseSize (EIA/JIS)	0805/2012
Inductance	22 μ H($\pm 20\%$)
Inductance Measuring Frequency	2.52MHz
Rated Current -Saturation Current	170mA
Rated Current -Temperature Rise Current	190mA
DC Resistance (max)	4.81 Ω
Avg. of DC.Resistance	3.7 Ω
Temperature Range	-40°C to 105°C
Self-resonant Frequency (min)	16MHz
RoHS Compliance	Yes
Halogen Free	Yes
Soldering Method	Reflow

■ External Dimensions

L	2mm ± 0.2
W	1.25mm ± 0.2
H	1.25mm ± 0.2

2013.10.15

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.
 TAIYO YUDEN reserves the right to make change to the Date at any time without notice.
 Before making final selection, please check product specification.