



Drawings not to scale  
All dimensions in mm (inches) nominal

## SPECIFICATION

CONTACT FORM/STYLE		Normally open
SWITCHING VOLTAGE	Max. Vac	24
SWITCHING CURRENT	Max. A	0.25
SWITCHING CAPACITY (RESISTIVE)	Max. VA	5
CONTACT RESISTANCE	Max. $\Omega$	10
OPERATING TEMPERATURE	Deg. $^{\circ}\text{C}$	$-20^{\circ} + 85^{\circ}$
STORAGE TEMPERATURE	Deg. $^{\circ}\text{C}$	$-25^{\circ} + 90^{\circ}$
ACTIVATION LEVELS	G	
OPTIONS	1	$5.5 \pm 1.5$
	2	$25.0 \pm 2.0$
	3	$45.0 \pm 3.0$
CASE MATERIAL		Steel - tin plated

NOTE: When cutting or bending switch leads it is important that the glass seal is not damaged. The cutting or bending point should be no closer than 3mm (.118) to the glass to metal seal and the lead should be supported between the cutting or bending point and the glass to metal seal.

### LINEAR ACCELERATION SWITCH

PART NUMBER  
**ASS**

Rev. No.	Revision Note	Date	Signature
C	Web Site 1999	1-5-99	RG

The Comus Group of Companies consist of:  
Assemtech Europe Limited  
E. Bachem GmbH  
Comus International  
W. Gunther GmbH  
Gunther Belgium  
Gunther France  
S.T.G.

As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and details of our full design and manufacturing service. All products are supplied to our standard conditions of sale otherwise agreed in writing.