



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: TLP604

6 outlet, 4-ft cord, 790 joule strip - Protect It! Surge Suppressor



Highlights

- 6 outlets / 4-ft. cord
- 790 joule rating
- \$20,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico & Canada only)

Description

Tripp Lite's TLP604 offers economical AC surge suppression for protection of workstations, desktop PCs, telecom systems and other sensitive electronics. Built-in AC surge suppression shields connected equipment from damage and performance problems due to transient surges. TLP604 offers 6 total outlets, 4 foot cord and diagnostic LED to warn of suppressor damage. AC suppression rated at 790 joules shields equipment from surges and line noise. Attractive white suppressor housing with keyhole mounting tabs and 1 designated transformer plug outlet offers convenient protection of desktop computer equipment and accessories. \$20,000 [Ultimate Lifetime Insurance](#) (USA & Canada Only).

PLUG/OUTLETS: Input: NEMA5-15P/Output: 6 NEMA5-15R/4-ft. AC line cord

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Corded multi-outlet strip

SUPPRESSION: AC: 150V RMS Clamping/790 joules/500V UL1449 Let-through

Applications

- Ideal for any desktop, network or home computing application requiring AC line protection.

Package Includes

- TLP604 Surge Suppressor
- Instruction manual with warranty information

Features

- 790 joules AC surge suppression shields equipment from the strongest surges and line noise
- 6 AC outlets with room for 1 transformer plugs without blocking outlets covers computers and peripherals
- 4 foot AC line cable
- Built-in power switch and 15 amp circuit breaker offers power control and overload protection over all outlets
- Fail-safe thermal fusing protects against fire and other damage in the event of an extreme, extended overvoltage or surge condition
- Diagnostic LEDs confirm surge suppression status
- Attractive white suppressor housing with keyhole mounting tabs allow versatile placement options
- UL1449 3rd Edition Rated (500V all modes), UL1363 (Power Tap), UL497A (Communications), Meets FCC part 68 rules, cUL (Canada)
- Exceeds IEEE 587 category A & B surge suppression specifications
- \$20,000 [Ultimate Lifetime Insurance](#) (USA and Canada Only)

Specifications

OVERVIEW	
Intended Application	Home/Office

OUTPUT	
Frequency compatibility	50 / 60 Hz
Output watts	1800
Circuit Breaker (amps)	15
Outlet quantity / type	6 NEMA 5-15R
Transformer accommodation	Supports 1 large transformer plug accessory without covering remaining outlets, accepts up to 4 transformers total
Outlet orientation	Single row
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P
Input cord length (ft.)	4
Input cord length (m)	1.22
Input cord gauge, type	14 gauge, SJT
Voltage compatibility (VAC)	120
Maximum Surge Amps	36000
LEDS ALARMS & SWITCHES	
Switches	Combination AC circuit breaker and 2 position on/off power switch
Diagnostic LEDs	Built-in LED confirms suppressor "protection present" (green) status
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	790
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping voltage (RMS)	150
UL1449 let through rating	500V
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Shipping Dimensions (HWD/in)	8 x 4 x 1.30
Shipping Dimensions (HWD/cm)	20.32 x 10.16 x 3.302
Shipping weight (lbs)	.86
Shipping weight (kg)	0.39

Unit Dimensions (HWD/in)	10.8 x 1.85 x 1.23
Unit Dimensions (HWD/cm)	27.43 x 4.70 x 3.12
Unit weight (lbs)	.80
Unit weight (kg)	0.36
Material of construction	Plastic
Integrated keyhole mounting tabs	Keyhole mounting tabs enable wall mounting
Housing Color	Light Gray
Receptacle Color	Light Gray
AC line cord color	Light Gray
Style	Strip
Outlets center to center measurement	28.5mm
Keyhole slot center to center measurement	Distance between slots = 101mm; Distance between slot height = 28mm
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3RD EDITION
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$20,000 Ultimate Lifetime Insurance

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=123.

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.