

General Purpose - Rapid Rack (C2RR Series)



**Rapid Rack
POPULAR STOCKED CONFIGURATIONS
(See Page 53 For Component Parts)**

FEATURES

- Heavy duty - welded frame - recommended maximum weight (C2F247836 tested) - 1,500 pounds (682 kg)
- Unit is shipped complete (**NO ASSEMBLY REQUIRED**)
- Choice of two depths 23.63" (600 mm) - 21.63" (549 mm) usable depth or 31.5" (800 mm) - 29.5" (749 mm) usable depth
- Standard 19" panel width - 23" (584 mm) overall
- **Unit includes:**
 - a welded steel rack frame
 - two (2) removable side panels (with 1/4 turn latches)
 - four (4) infinitely adjustable, tapped combination rack mount rails (full E.I.A. spacing)
 - one (1) solid flush mount door (can be either front or back as rack is symmetrical) - locking with two (2) keys
 - solid top
 - four (4) leveling feet
- Heavy duty 14 gauge steel frame
- Formed 16 gauge steel side panels are recessed to fit flush with the sides of the cabinet
- Welded corner reinforcements
- Opening in bottom for cable entry
- Panel rails are zinc plated, 10 gauge steel, drilled and tapped 10-32
- Finished in a rugged, textured powder paint

UNIVERSAL ACCESSORIES

- Rack panels [Page 90](#)
- Ventilated rack panels [Page 92](#)
- Panel mount doors & chassis [Page 94](#)
- Shelves & slides [Page 95](#)
- Drawers [Page 101](#)
- Cable management [Page 102](#)
- Cooling [Page 105](#)
- Rack mount outlet strips [Page 110](#)
- Hardware [Page 127](#)
- Exclusive to this series [Page 53](#)
- Visit our web site for our most [recent accessories](#)

ASSEMBLED
Shipped on its own skid
for handling ease &
protection
FROM STOCK!



Assembled

Welded

42



CANADA

Guelph, Ontario (519) 822-2960
St. Laurent, Quebec (514) 343-9010

USA

Cheektowaga, NY (716) 630-7030



EUROPE


Basingstoke, UK 01256 812812

AUSTRALIA


Queenstown SA, Australia 61-8-8240-2244

General Purpose - Rapid Rack (C2RR Series)


Front View




Side View
(Side Panel
Not Shown)



Bottom View



Top View
(Top Cover
Not Shown)



23.63" (600 mm) Deep - Usable Depth = 21.63" (549 mm)

Part Number		Panel Height		Overall Dimensions			Weight
Black Textured	Light Gray Textured	Inches	Units	Height (A)	Width (B)	Panel Opening (D)	
C2RR194223BK1	C2RR194223LG1	42"	24U	49.31" (1,252 mm)	23.0" (584 mm)	42.06" (1,068 mm)	170# (77 kg)
C2RR196323BK1	C2RR196323LG1	63"	36U	70.31" (1,786 mm)	23.0" (584 mm)	63.06" (1,602 mm)	218# (99 kg)
C2RR197023BK1	C2RR197023LG1	70"	40U	77.31" (1,964 mm)	23.0" (584 mm)	70.06" (1,780 mm)	230# (105 kg)
C2RR197823BK1	C2RR197823LG1	78.75"	45U	86.06" (2,186 mm)	23.0" (584 mm)	78.81" (2,002 mm)	254# (116 kg)

31.5" Deep (800 mm) - Usable Depth = 29.5" (749 mm)

Part Number		Panel Height		Overall Dimensions			Weight
Black Textured	Light Gray Textured	Inches	Units	Height (A)	Width (B)	Panel Opening (D)	
C2RR194231BK1	C2RR194231LG1	42"	24U	49.31" (1,252 mm)	23.0" (584 mm)	42.06" (1,068 mm)	194# (88 kg)
C2RR196331BK1	C2RR196331LG1	63"	36U	70.31" (1,786 mm)	23.0" (584 mm)	63.06" (1,602 mm)	250# (114 kg)
C2RR197031BK1	C2RR197031LG1	70"	40U	77.31" (1,964 mm)	23.0" (584 mm)	70.06" (1,780 mm)	268# (122 kg)
C2RR197831BK1	C2RR197831LG1	78.75"	45U	86.06" (2,186 mm)	23.0" (584 mm)	78.81" (2,002 mm)	290# (132 kg)

Assembled

Welded

EUROPE

Basingstoke, UK 01256 812812

AUSTRALIA

Queenstown SA, Australia 61-8-8240-2244



CANADA

Guelph, Ontario (519) 822-2960
St. Laurent, Quebec (514) 343-9010

USA

Cheektowaga, NY (716) 630-7030

