

We measure it.



Temperature measuring instrument (1-channel)

testo 925 - For fast and reliable measurements in the HVAC field

Ideally suited to applications in the HVAC field

1-channel temperature measuring instrument with optional wireless probes


TopSafe, the indestructible protective case, protects from dirt and impact

Continuous display of min/max values

Audible alarm (adjustable limit values)

Hold-button for freezing measurement values

Large, backlit display



Technical data

testo 925

testo 925, 1 channel temperature measuring instrument T/C Type K, audible alarm, connection of an optional radio probe, with battery and calibration protocol

Part no. 0560 9250



Sensor type Type K (NiCr-Ni)

Meas. range	-50 to +1000 °C
Accuracy ±1 digit	±(0.5 °C +0.3% of mv) (-40 to +900 °C) ±(0.7 °C +0.5% of mv) (remaining range)
Resolution	0.1 °C (-50 to +199.9 °C) 1 °C (remaining range)

General technical data

Oper. temp.	-20 to +50 °C
Storage temp.	-40 to +70 °C
Material/Housing	ABS
Battery type	9V block battery, 6F22
Battery life	200 h (connected probe, backlight off) 45 h (radio mode, backlight off) 68 h (connected probe, backlight always on) 33 h (radio mode, backlight always on)
Dimensions	182 x 64 x 40 mm
Weight	171 g
Warranty	2 years

The testo 925 is a 1-channel temperature measuring instrument which is particularly suitable for applications in the HVAC field. The instrument is optimum for the connection of fast and reliable thermocouple probes. Using measurement data transfer by radio, the measurement value of a further temperature probe can be additionally displayed wirelessly. The protective cover TopSafe ensures water- and dirt-proofness when a probe is connected. The instrument

reliably and continuously displays the minimum and maximum measurement values. The measurement values shown in the display (current measurement value, frozen measurement value, or the minimum/maximum values) can be printed out via the Testo report printer (optional). The user can store limit values in the instrument himself; as soon as these upper and lower values are violated, an audible signal sounds.



Optional protective case TopSafe



Wireless measurement with radio probes



1 probe connection


Accessories

Accessories for measuring instrument	Part no.	
9V rech. battery for instrument, instead of battery	0515 0025	
Recharger for 9V rechargeable battery for external recharging of 0515 0025 battery	0554 0025	
Radio module for upgrading measuring instrument with radio option		
Radio module for measuring instrument, 869.85 MHz, approval for the countries: DE, FR, UK, BE, NL, ES, IT, SE, AT, DK, FI, HU, CZ, PL, GR, CH, PT, SI, MT, CY, SK, LU, EE, LT, IE, LV, NO	0554 0188	
Radio module for measuring instrument, 915.00 MHz FSK, approval for USA, CA, CL	0554 0190	
Printer and Accessories		
Testo fast printer with wireless infrared interface, 1 roll thermal paper and 4 AA batteries	0554 0549	
Spare thermal paper for printer (6 rolls), permanent ink measurement data documentation legible for up to 10 years	0554 0568	
Transport and Protection		
TopSafe, protects from impact and dirt	0516 0221	
Transport case for measuring instrument, 3 probes and accessories (430 x 310 x 85 mm)	0516 0200	
Transport case for meas. instr. and probes (405 x 170 x 85 mm)	0516 0201	
Case for measuring instrument and probes	0516 0210	
Other features		
Handle for attachable measurement tips	0409 1092	
Extension cable, 5m, for thermocouple probe Type K	0554 0592	
Silicone heat paste (14g), Tmax = +260°C, improves heat transfer in surface probes	0554 0004	
Calibration Certificates		
ISO calibration certificate/temperature for air/immersion probes, calibration points -18°C; 0°C; +60°C	0520 0001	
ISO calibration certificate/temperature (Applies only to immersion/penetration probe 0602 2693) Meas. instr. with air/immersion probe; cal. points 0°C; +150°C; +300°C	0520 0021	
ISO calibration certificate/temperature meas. instr. with air/immersion probe; calibration points 0°C; +300°C; +600°C	0520 0031	
ISO calibration certificate/temperature meas. instr. with surface probe; calibration points +60°C; +120°C; +180°C	0520 0071	
DAkkS calibration certificate/temperature meas. instr. with air/immersion probe; calibration points -20 °C; 0 °C; +60 °C	0520 0211	
DAkkS calibration certificate/temperature contact surface temperature probes; calibration points +100°C; +200°C; +300°C	0520 0271	

Radio probes


Radio probes for immersion/penetration measurements

Part no.

Radio immersion/penetration probe, NTC, approval for the countries: DE, FR, UK, BE, NL, ES, IT, SE, AT, DK, FI, HU, CZ, PL, GR, CH, PT, SI, MT, CY, SK, LU, EE, LT, IE, LV, NO; Radio freq. 869.85 MHz FSK					0613 1001
Radio immersion/penetration probe, NTC, approval for USA, CA, CL; Radio freq. 915.00 MHz FSK					0613 1002
Dimensions Probe shaft/probe shaft tip	Measuring range	Accuracy	Resolution	t ₉₉	
	-50 to +275 °C	±0.5 °C (-20 to +80 °C) ±0.8 °C (-50 to -20.1 °C) ±0.8 °C (+80.1 to +200 °C) ±1.5 °C (remaining range)	0.1 °C	t ₉₉ (in water) 12 s	


Radio handles with probe head for air-/ immersion-penetration-meas.

Part no.

Radio handle for plug-in probe heads, incl. T/C adapter, approval for the countries: DE, FR, UK, BE, NL, ES, IT, SE, AT, DK, FI, HU, CZ, PL, GR, CH, PT, SI, MT, CY, SK, LU, EE, LT, IE, LV, NO; Radio freq. 869.85 MHz FSK					0554 0189
T/C probe head for air/immersion/penetration measurement, attachable to radio handle, T/C Type K					0602 0293
Radio handle for plug-in probe heads, incl. T/C adapter, approval for USA, CA, CL; Radio freq. 915.00 MHz FSK					0554 0191
T/C probe head for air/immersion/penetration measurement, attachable to radio handle, T/C Type K					0602 0293
Dimensions Probe shaft/probe shaft tip	Measuring range	Accuracy	Resolution	t ₉₉	
	-50 to +350 °C Short-term to +500 °C	Radio handle: ±(0.5 °C +0.3% of mv) (-40 to +500 °C) ±(0.7 °C +0.5% of mv) (remaining range) T/C probe head: Class 2	0.1 °C (-50 to +199.9 °C) 1.0 °C (remaining range)	t ₉₉ (in water) 10 s	


Radio handles with probe head for surface measurement

Part no.

Radio handle for plug-in probe heads, incl. T/C adapter, approval for the countries: DE, FR, UK, BE, NL, ES, IT, SE, AT, DK, FI, HU, CZ, PL, GR, CH, PT, SI, MT, CY, SK, LU, EE, LT, IE, LV, NO; Radio freq. 869.85 MHz FSK					0554 0189
T/C probe head for surface measurement, attachable to radio handle, T/C Type K					0602 0394
Radio handle for plug-in probe heads, incl. T/C adapter, approval for USA, CA, CL; Radio freq. 915.00 MHz FSK					0554 0191
T/C probe head for surface measurement, attachable to radio handle, T/C Type K					0602 0394
Dimensions Probe shaft/probe shaft tip	Measuring range	Accuracy	Resolution	t ₉₉	
	-50 to +350 °C Short-term to +500 °C	Radio handle: ±(0.5 °C +0.3% of mv) (-40 to +500 °C) ±(0.7 °C +0.5% of mv) (remaining range) T/C probe head: Class 2	0.1 °C (-50 to +199.9 °C) 1.0 °C (remaining range)	5 s	

Radio handles for attachable T/C probes

Part no.

Radio handle for plug-in probe heads, incl. T/C adapter, approval for the countries: DE, FR, UK, BE, NL, ES, IT, SE, AT, DK, FI, HU, CZ, PL, GR, CH, PT, SI, MT, CY, SK, LU, EE, LT, IE, LV, NO ; Radio freq. 869.85 MHz FSK					0554 0189
Radio handle for plug-in probe heads, incl. T/C adapter, approval for USA, CA, CL; Radio freq. 915.00 MHz FSK					0554 0191
Illustration	Measuring range	Accuracy	Resolution		
	-50 to +1000 °C	±(0.7 °C +0.3% of mv) (-40 to +900 °C) ±(0.9 °C +0.5% of mv) (remaining range)	0.1 °C (-50 to +199.9 °C) 1.0 °C (remaining range)		

Technical data Radio probes

Radio immersion/penetration probe, NTC

Battery type	2 x 3V button cell (CR 2032)
Battery life	150 h (meas. rate 0.5 s) 2 months (meas. rate 10 s)











Radio handle

Battery type	2 AAA micro batteries
Battery life	215 h (meas. rate 0.5 s) 6 months (meas. rate 10 s)

Common Technical Data










Measuring rate	0.5 s or 10 s, adjustable on handle
Radio coverage	Up to 20 m (without obstructions)
Radio transmission	Unidirectional
Oper. temp.	-20 to +50 °C
Storage temp.	-40 to +70 °C

Probes

Probe type	Dimensions Probe shaft/probe shaft tip	Measuring range	Accuracy	t99	Part no.
Air probes					
<ul style="list-style-type: none"> Robust air probe, T/C Type K, Fixed cable 1.2 m 		-60 to +400 °C	Class 2 ¹⁾	25 s	0602 1793
Immers./penetr. probes					
<ul style="list-style-type: none"> Efficient and fast-action immersion probe, waterproof, TC Type K, Fixed cable 1.2 m 		-60 to +1000 °C	Class 1 ¹⁾	2 s	0602 0593
<ul style="list-style-type: none"> Fast-action, waterproof immersion/penetration probe, TC Type K, Fixed cable 1.2 m 		-60 to +800 °C	Class 1 ¹⁾	3 s	0602 2693
Immersion tip, flexible, TC Type K		-200 to +1000 °C	Class 1 ¹⁾	5 s	0602 5792
Immersion measurement tip, flexible, for measurements in air/exhaust gases (not suitable for measurements in smelters), TC Type K		-200 to +1300 °C	Class 1 ¹⁾	4 s	0602 5693
Immersion tip, flexible, TC Type K		-200 to +40 °C	Class 3 ¹⁾	5 s	0602 5793
<ul style="list-style-type: none"> Waterproof immersion/penetration probe, TC Type K, Fixed cable 1.2 m 		-60 to +400 °C	Class 2 ¹⁾	7 s	0602 1293
Surface probes					
<ul style="list-style-type: none"> Fast-reaction paddle surface probe, for measurements in inaccessible places, e.g. narrow apertures and slots, TC Type K, Fixed cable 		0 to +300 °C	Class 2 ¹⁾	5 s	0602 0193
<ul style="list-style-type: none"> Fast-action surface probe with sprung thermocouple strip, also for uneven surfaces, measurement range short-term to +500°C, TC Type K, Fixed cable 1.2 m 		-60 to +300 °C	Class 2 ¹⁾	3 s	0602 0393
<ul style="list-style-type: none"> Waterproof surface probe with widened measurement tip for flat surfaces, T/C Type K, Fixed cable 1.2 m 		-60 to +400 °C	Class 2 ¹⁾	30 s	0602 1993







- The measuring instrument inside TopSafe is waterproof with this probe.
- 1) According to standard EN 60584-2, the accuracy of Class 1 refers to -40 to +1000 °C (Type K), Class 2 to -40 to +1200 °C (Type K), Class 3 to -200 to +40 °C (Type K).

Probes

Probe type	Dimensions Probe shaft/probe shaft tip	Measuring range	Accuracy	t99	Part no.
Surface probes					
<p>◆ Fast-action surface probe with sprung thermocouple strip, bent, also for uneven surfaces, measurement range short-term to +500°C, TC Type K, Fixed cable 1.2 m</p>		-60 to +300 °C	Class 2 ¹⁾	3 s	0602 0993
<p>◆ Efficient, waterproof surface probe with small measurement head for flat surfaces, TC Type K, Fixed cable 1.2 m</p>		-60 to +1000 °C	Class 1 ¹⁾	20 s	0602 0693
<p>Flat head surface probe with telescopic handle max. 680 mm for measurements at hard-to-access points, TC Type K, Fixed cable 1.6 m (correspondingly shorter when telescope extended)</p>		-50 to +250 °C	Class 2 ¹⁾	3 s	0602 2394
<p>Magnetic probe, adhesive force approx. 20 N, with magnets, for measurements on metal surfaces, TC Type K, Fixed cable 1.6 m</p>		-50 to +170 °C	Class 2 ¹⁾	150 s	0602 4792
<p>Magnetic probe, adhesive force approx. 10 N, with magnets, for higher temp., for measurements on metal surfaces, TC Type K, Fixed cable</p>		-50 to +400 °C	Class 2 ¹⁾		0602 4892
<p>Pipe wrap probe with Velcro strip, for temperature measurement on pipes with diameter up to max. 120 mm, Tmax +120°C, TC Type K, Fixed cable</p>		-50 to +120 °C	Class 1 ¹⁾	90 s	0628 0020
<p>Pipe wrap probe for pipe diameter 5 to 65 mm, with exchangeable measuring head. Meas. range short-term to +280°C, TC Type K, Fixed cable</p>		-60 to +130 °C	Class 2 ¹⁾	5 s	0602 4592
<p>Spare meas. head for pipe wrap probe, TC Type K</p>		-60 to +130 °C	Class 2 ¹⁾	5 s	0602 0092
<p>Clamp probe for measurements on pipes, pipe diameter 15 to 25 mm (max. 1"), meas. range short-term up to +130°C, TC Type K, Fixed cable</p>		-50 to +100 °C	Class 2 ¹⁾	5 s	0602 4692

◆ The measuring instrument inside TopSafe is waterproof with this probe.
 1) According to standard EN 60584-2, the accuracy of Class 1 refers to -40 to +1000 °C (Type K), Class 2 to -40 to +1200 °C (Type K), Class 3 to -200 to +40 °C (Type K).

Probes

Probe type	Dimensions Probe shaft/probe shaft tip	Measuring range	Accuracy	t99	Part no.
Food probes					
♦ Waterproof food probe made of stainless steel (IP65), TC Type K, Fixed cable		-60 to +400 °C	Class 2 ¹⁾	7 s	0602 2292
Robust food probe with special handle, IP 65, reinforced cable (PUR), T/C Type K, Fixed cable		-60 to +400 °C	Class 1 ¹⁾	6 s	0602 2492
Waterproof robust immersion/penetration probe with metal protection hose Tmax +230°C, e.g. for monitoring temp. in cooking oil, T/C Type K, Fixed cable		-50 to +230 °C	Class 1 ¹⁾	15 s	0628 1292
Thermocouples					
Thermocouple with TC adapter, flexible, 800mm long, fibre glass, TC Type K		-50 to +400 °C	Class 2 ¹⁾	5 s	0602 0644
Thermocouple with TC adapter, flexible, 1500mm long, fibre glass, TC Type K		-50 to +400 °C	Class 2 ¹⁾	5 s	0602 0645
Thermocouple with TC adapter, flexible, 1500mm long, PTFE, TC Type K		-50 to +250 °C	Class 2 ¹⁾	5 s	0602 0646

♦ The measuring instrument inside TopSafe is waterproof with this probe.

1) According to standard EN 60584-2, the accuracy of Class 1 refers to -40 to +1000 °C (Type K), Class 2 to -40 to +1200 °C (Type K), Class 3 to -200 to +40 °C (Type K).

