



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: SMART1000RM2U

**SmartPro 1kVA 800W Line Interactive Sine Wave UPS, SNMPWEBCARD option, 2U Rack/Tower, LCD, USB, RS232, EPO, 120V**

### Highlights

- 1kVA / 1000VA / 800W line interactive 2U rack/tower UPS, Sine Wave
- 120V output, Corrects brownouts and overvoltages from 83V to 147V
- 0.8 Power Factor, Interactive LCD interface
- 4 post compatible mounting accessories
- 95% line-mode efficiency, 2 switched load banks
- USB, RS232, EPO and slot for SNMPWEBCARD option
- 120V NEMA 5-15P input, 6 NEMA 5-15R outlets



### Description

Tripp Lite SmartPro Line Interactive UPS with enhanced LCD interface offers network-grade power protection for critical server, network and telecommunications equipment. Line Interactive Uninterruptible Power Supply (UPS) with built-in Auto-Voltage Regulation (AVR) actively corrects brownouts and overvoltages back to usable levels while maintaining a full battery charge in case of power failure. Interactive LCD interface reports UPS operating mode, detailed UPS and site-power data, plus enables a variety of UPS setup and configuration options. Super-fast switchover from line to battery power occurs within milliseconds to maintain operation of connected equipment without interruption or reboot. 95% line-mode efficiency offers reduced heat emissions and operating costs. Network management interfaces support communications via USB, RS-232 and optional SNMPWEBCARD network interface. HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X. Network communications ports enable detailed monitoring of equipment load levels, self-test data and utility power conditions. Includes PowerAlert monitoring software and complete cabling. Switched output load banks enable scheduled and real-time remote reboot and load shedding of select outlets. Emergency Power Off (EPO) interface. LCD display panel easily rotates for viewing in rackmount or tower configurations. Audible alarm with push-button momentary alarm-cancel and silent-mode configuration options. Programmable self-test. Field-replaceable, hot-swappable battery modules.

### Package Includes

- SMART1000RM2U UPS System
- PowerAlert software with USB, Serial & EPO cabling
- 4 post rackmount installation kit
- Instruction manual

### Features

- Tripp Lite SMART1000RM2U line interactive 2U rack/tower UPS with 1000VA / 1kVA / 800W capacity
- Line interactive UPS with Automatic Voltage Regulation (AVR) corrects brownouts and overvoltages from 83 to 145V
- NEMA 5-15P input plug; 6 NEMA 5-15R output receptacles, Two independently switchable output load banks
- Maintains uninterrupted operation of connected networking equipment during blackouts, surges, brownouts and overvoltages
- High 95% efficiency rating in line-power mode offers reduced power consumption and BTU emissions
- Internal batteries offer 15 minutes at 50% load (400W) and 5.3 minutes at 100% load (800W)
- Hot-swappable, user-replaceable internal batteries can be replaced with no disruption to connected equipment
- Front panel LCD monitoring screen with MODE and ENTER buttons reports operating mode with 5-bar battery charge graphic, plus 7 selectable screens of detailed UPS and site power information
- LCD interface also supports a number of advanced user setup and operating preferences
- Ships with 4 post rackmount installation hardware; Optional 2POSTRMKITWM enables 2 post rackmount/wallmount installation; Optional 2-9USTAND enables tower placement
- Built-in USB, RS-232 and optional SNMPWEBCARD accessory monitoring options
- HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X

- Included PowerAlert UPS monitoring software; Built-in Emergency Power Off (EPO) interface with cable

## Specifications

<b>OUTPUT</b>	
Output Volt Amp Capacity (VA)	1000
Output kVA capacity (kVA)	1.0
Output Watt Capacity (watts)	800
Output power factor	0.8
Nominal Output Voltage(s) Supported	120V
Frequency compatibility	60 Hz
Output voltage regulation (line mode)	-21%, +8%
Output voltage regulation (Battery mode)	+/- 5%
Built-in UPS output receptacles	6 5-15R outlet(s)
Built-in controllable switched load banks	Two switchable two-outlet 5-15R load banks
Output AC waveform (AC mode)	Sine wave
Output AC waveform (battery mode)	Pure Sine wave
<b>INPUT</b>	
Rated input current (at maximum load)	9.2A
Nominal Input Voltage(s) Supported	120V AC
UPS input connection type	5-15P
Input circuit breaker	15A
UPS Input cord length (ft.)	10
UPS Input cord length (m)	3
Recommended Electrical Service	15A 120V
<b>BATTERY</b>	
Full load runtime (minutes)	5.3 min. (800w)
Half load runtime (minutes)	15 min. (400w)

<b>DC system voltage (VDC)</b>	24
<b>Battery recharge rate (included batteries)</b>	Less than 4 hours from 10% to 90%
<b>Replacement battery cartridge (internal UPS battery replacement)</b>	See Tripp Lite UPS Replacement battery selector
<b>Battery Access</b>	Front panel battery access door
<b>Battery replacement description</b>	Hot-swappable, user replaceable batteries
<b>VOLTAGE REGULATION</b>	
<b>Voltage regulation description</b>	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 83 to 147
<b>Overvoltage correction</b>	Input voltages between 128 and 147 are reduced by 12%
<b>Undervoltage correction</b>	Input voltages between 83 and 107 are boosted by 14%
<b>LEDS ALARMS &amp; SWITCHES</b>	
<b>Front panel LCD display</b>	Front panel LCD information and configuration screen offers detailed UPS and site power status and operating data, plus configuration of voltage, operating mode, alarm function and a variety of additional options (see manual for detailed LCD configuration and monitoring options)
<b>Alarms</b>	Audible alarm indicates UPS startup, power-failure, low-battery, overload, UPS fault and remote shutdown conditions
<b>Alarm cancel operation</b>	Power-fail alarm can be temporarily silenced using alarm-cancel switch; silent mode alarm configuration option available
<b>Switches</b>	3 pushbutton switches control OFF / ON power status, MODE selection and MUTE / ENTER control functions
<b>SURGE / NOISE SUPPRESSION</b>	
<b>UPS AC suppression joule rating</b>	570
<b>UPS AC suppression response time</b>	Instantaneous
<b>EMI / RFI AC noise suppression</b>	Yes
<b>PHYSICAL</b>	
<b>Installation form factors supported with included accessories</b>	4 post 19 inch rackmount (mounting rail kit included)
<b>Installation form factors supported with optional accessories</b>	2 post rackmount (2POSTRMKITWM); Wallmount (2POSTRMKITWM); Tower (2-9USTAND)
<b>Primary form factor</b>	Rackmount
<b>UPS / Power Module dimensions in primary form factor (height x width x depth / inches)</b>	3.5 x 17.5 x 12.5

<b>UPS / Power Module dimensions in primary form factor (height x width x depth / cm)</b>	8.9 x 44.4 x 31.75
<b>Rack Height</b>	2U
<b>Secondary form factor</b>	Tower (requires <a href="#">2-9U STAND</a> )
<b>UPS / Power Module weight (lbs)</b>	35.4
<b>UPS / Power Module weight (kg)</b>	16.1
<b>UPS Shipping dimensions (height x width x depth / inches)</b>	9 x 24 x 20.2
<b>UPS Shipping dimensions (height x width x depth / cm)</b>	22.9 x 61 x 51.4
<b>Shipping weight (lbs)</b>	46.4
<b>Shipping weight (kg)</b>	21.1
<b>Cooling method</b>	Fan
<b>UPS housing material</b>	Steel
<b>ENVIRONMENTAL</b>	
<b>Operating Temperature Range</b>	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
<b>Storage Temperature Range</b>	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
<b>Relative Humidity</b>	0 to 95%, non-condensing
<b>AC mode BTU / hr. (full load)</b>	134
<b>COMMUNICATIONS</b>	
<b>Communications interface</b>	USB; DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface
<b>Network monitoring port description</b>	Supports detailed monitoring of UPS and site power conditions
<b>PowerAlert software</b>	Included
<b>Communications cable</b>	USB and DB9 cabling included
<b>WatchDog compatibility</b>	Supports Watchdog application, OS and hard-reboot restart options for remote applications
<b>LINE / BATTERY TRANSFER</b>	
<b>Transfer time</b>	4 milliseconds (AC to battery), 2 milliseconds (Battery to AC)
<b>Low voltage transfer to battery power (setpoint)</b>	83

High voltage transfer to battery power (setpoint)	147
<b>SPECIAL FEATURES</b>	
Grounding lug	Back panel grounding lug
Cold Start (startup in battery mode during a power failure)	Cold-start operation supported
High availability UPS features	Hot swappable batteries
Green & high efficiency features	Individually controllable load banks
<b>CERTIFICATIONS</b>	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year warranty, 3 year with <a href="#">registration</a> . Note: <a href="#">registration</a> is required for 3-year warranty.
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 <a href="#">Ultimate Lifetime Insurance</a>

## Related Items

### Optional Products

Related Model	Description	Qty.
<a href="#">WEXT5-500-1500</a>	5-Year Extended Warranty - For Smart Line-Interactive and Online Tower or Rack models, 1500VA or less	1
<a href="#">SNMPWEBCARD</a>	For remote monitoring and control via SNMP, Web, or Telnet.	1
<a href="#">ENVIROSENSE</a>	Monitors temperature, humidity and contact-closure inputs. (Requires SNMPWEBCARD or switched PDU.)	1
<a href="#">2-9USTAND</a>	Enables Tower Placement of Rackmount UPS Systems	1
<a href="#">2POSTRMKITWM</a>	Enables 2-Post Rackmount or Wallmount Installation of Select Rackmount UPS Systems	1
<a href="#">RBC24V-LCD</a>	2U UPS Replacement Battery Cartridge for select Tripp Lite SmartPro UPS	1
<a href="#">WATCHDOGSW</a>	WatchDog Service Monitoring / Reboot Software	1
<a href="#">PDUB15</a>	Single-Phase Hot-Swap PDU, 15A 120V, 2U Horizontal Rackmount, 8 NEMA 5-15R outlets, set of 2 NEMA 5-15P input plugs	1
<a href="#">PDU1215</a>	Basic PDU / Power Distribution Unit - Safe, reliable power distribution for critical networking equipment	1
<a href="#">PDUNV</a>	Basic PDU / Power Distribution Unit - Safe, reliable power distribution for critical networking equipment	1
<a href="#">PDUMH15</a>	Metered PDU / Power Distribution Unit - Safe, reliable power distribution with digital current meter	1
<a href="#">PDUMH15AT</a>	Metered PDU with ATS - Power Distribution Unit with dual-input Auto Transfer Switching	1
<a href="#">PDUMNH15</a>	Monitored PDU / Power Distribution Unit supports real-time remote monitoring of load level, voltage and frequency with options for remote environmental and security monitoring	1

PDUMNV15	Monitored PDU / Power Distribution Unit supports real-time remote monitoring of load level, voltage and frequency with options for remote environmental and security monitoring	1
PDUMH15ATNET	Switched, Metered PDU with ATS - Power Distribution Unit with dual-input Auto Transfer Switching, individual outlet control and remote network interface	1
PDUMV15NET	Switched, Metered PDU with Remote Monitoring - 0U Vertical Rackmount Power Distribution Unit for Networks with Individually Switchable Outlets, Current Metering, Remote Monitoring and Control	1
P007-002	2-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	1
P007-006	6-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	1
P007-010	10-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to NEMA 5-15P)	1
P010-012	12-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13)	1
P022-001	1-ft. 18AWG Power Extension cord (NEMA 5-15R to NEMA 5-15P)	1
P023-001	1-ft. 14AWG Power Adapter cord (NEMA L5-15R to NEMA 5-15P)	1
P034-010	10-ft. 14AWG Heavy Duty Power cord (IEC-320-C19 to NEMA 5-15P)	1
P006-006-13LA	6-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13 Left Angle)	1
P006-006-13RA	6-ft. 18AWG Power cord (NEMA 5-15P to IEC-320-C13 Right Angle)	1
P019-004	4-ft. Heavy Duty 14AWG Power Cord, 5-15P - to - C15	1
P019-008	8-ft. Heavy Duty 14AWG Power Cord, 5-15P - to - C15	1
UPSHDEARKIT	Heavy-Duty 2-post Front Mounting Ear Kit	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=2657](http://www.tripplite.com/en/products/model.cfm?txtModelID=2657).

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.