

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [45750-3211](#)  
**Status:** **Active**  
**Overview:** [Mini-Fit® Plus Connector System](#)  
**Description:** [Mini-Fit® Plus Crimp Terminal, 16 AWG, Reel, Copper \(Cu\) Alloy, Gold \(Au\) Selective](#)

**Documents:**

[Drawing \(PDF\)](#)      [Packaging Specification PK-45750-001 \(PDF\)](#)  
[Product Specification PS-45750-001 \(PDF\)](#)      [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Crimp Terminals
Series	<a href="#">45750</a>
Application	Power
Comments	Current = 13A max. per circuit when header is mated to a receptacle loaded with <a href="#">45750</a> series terminals crimped to 16 AWG wire. . See Molex product specification PS-45750-001 for additional current derating information.
Crimp Quality Equipment Overview	Yes
Packaging Alternative	<a href="#">Mini-Fit® Plus Connector System</a>
Product Name	<a href="#">45750-3212 (Loose)</a>
UPC	Mini-Fit® Plus 822350286077

**Physical**

Durability (mating cycles max)	250
Gender	Female
Material - Metal	Copper-Nickel-Silicon
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.148/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	3.50mm
Wire Size AWG	16
Wire Size mm²	N/A

**Electrical**

Current - Maximum per Contact	13A
Voltage - Maximum	600V

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	PK-45750-001
Product Specification	PS-45750-001
Sales Drawing	SD-45750-001




image - Reference only

Series

**EU RoHS**

**ELV and RoHS Compliant**

**REACH SVHC Contains SVHC: No Low-Halogen Status Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[45750Series](#)

**Mates With**

[46012](#) Mini-Fit® Plus Crimp Terminal

**Use With**

[5557](#) Mini-Fit Jr.™, [30067](#) Mini-Fit® TPA, [42474](#) Mini-Fit® BMI Panel Mount, [43760](#) Mini-Fit® BMI, [44516](#) Mini-Fit® BMI Panel Mount Slide-N-Lock

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Extraction Tool	<a href="#">0011030044</a>
Hand Crimp Tool for Male and Female Crimp Terminals, 16-24 AWG Wire	<a href="#">0638190900</a>

FineAdjust™ Applicator for Insulation OD 2.60-3.15mm Optimized for 16 AWG Only	<u>0639002800</u>
FineAdjust™ Applicator for Insulation OD 2.20-2.45mm Optimized for 16 AWG Only	<u>0639003000</u>
FineAdjust™ Applicator for Insulation OD 1.80-2.20mm Optimized for 16 AWG Only	<u>0639015300</u>
T2 Terminator™ for insulation OD 2.60-3.15mm optimized for 16 AWG only	<u>0639102800</u>
T2 Terminator™ for insulation OD 2.20-2.45mm optimized for 16 AWG only	<u>0639103000</u>

This document was generated on 09/13/2013

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**