

Spezifikation für Freigabe / specification for release

Kunde / customer :

Artikelnummer / part number : **744324033**

LF




Bezeichnung : **SPEICHERDROSSEL WE-HC**

description : **POWER-CHOKE WE-HC**

WÜRTH ELEKTRONIK

DATUM / DATE : 2007-11-01

A Mechanische Abmessungen / dimensions :




Dimension	Value	Unit
A	10,5 ± 0,4	mm
B	10,0 ± 0,3	mm
C	3,8 ± 0,3	mm
D	2,2 ± 0,2	mm
E	5,4 ± 0,8	mm
F	5,0 ± 0,3	mm
G		mm
H		mm

B Elektrische Eigenschaften / electrical properties :

Eigenschaften / properties	Testbedingungen / test conditions		Wert / value	Einheit / unit	tol.
Induktivität / inductance	100 kHz / 0,1V	L _o	0,39	μH	± 20%
Nenn-Induktivität / rated inductance	100 kHz / 0,1V / 22A	L _N	0,30	μH	± 20%
DC-Widerstand / DC-resistance	@ 20° C	R _{DC}	1,36	mΩ	± 8%
Nennstrom / rated current	ΔT = 50 K	I _{DC}	22,0	A	typ.
Sättigungsstrom / saturation current	ΔL/L _o = -30%	I _{sat}	56,0	A	typ.
Eigenres.-Frequenz / self.res.-frequency		SRF	174,0	MHz	ref.

C Lötpad / soldering spec. :



D Prüfgeräte / test equipment :

HP 4274 A für/for L und/and Q
HP 34401 A für/for I_{DC} und/and R_{DC}

E Testbedingungen / test conditions :

Luftfeuchtigkeit / humidity: 33%
Umgebungstemperatur / temperature: + 25°C

F Werkstoffe & Zulassungen / material & approvals :

Kernmaterial / core material: WE-Superflux 200
Draht / wire: Flatwire/ Flachdraht UL94-V0; 2UEWF 155°C

G Eigenschaften / granted properties :

Arbeitstemperatur / operating temperature: -40°C - +150°C
Umgebungstemp. / ambient temperature: -40°C - +100°C
It is recommended that the temperature of the part does not exceed 150°C under worst case operating conditions.

Freigabe erteilt / general release:		Kunde / customer	
.....		
Datum / date	Unterschrift / signature	
.....		Würth Elektronik	
.....		
Geprüft / checked	Kontrolliert / approved	
.....		
Name	Änderung / modification	Datum / date	

Würth Elektronik eiSos GmbH & Co. KG

D-74638 Waldenburg · Max-Eyth-Strasse 1 - 3 · Germany · Telefon (+49) (0) 7942 - 945 - 0 · Telefax (+49) (0) 7942 - 945 - 400
<http://www.we-online.com>

Spezifikation für Freigabe / specification for release

Kunde / customer :

Artikelnummer / part number : **744324033**

LF




Bezeichnung : **SPEICHERDROSSEL WE-HC**

description : **POWER-CHOKER WE-HC**

WÜRTH ELEKTRONIK

DATUM / DATE : 2007-11-01

H Induktivitätskurve / Inductance curve :



Freigabe erteilt / general release:	Kunde / customer			
Datum / date	Unterschrift / signature	ME	Ver 6	2007-10-01
		RST	Version 5	2006-06-02
		ME	Version 4	2005-04-18
		MST	Version 3	2004-10-11
		SST	Version 2	2004-02-02
		JH	Version 1	2000-12-06
Geprüft / checked	Kontrolliert / approved	Name	Änderung / modification	Datum / date

Würth Elektronik eiSos GmbH & Co. KG

D-74638 Waldenburg · Max-Eyth-Strasse 1 - 3 · Germany · Telefon (+49) (0) 7942 - 945 - 0 · Telefax (+49) (0) 7942 - 945 - 400
http://www.we-online.com

Spezifikation für Freigabe / specification for release

Kunde / customer :

Artikelnummer / part number :

744324033

LF




Bezeichnung :

description :

WÜRTH ELEKTRONIK

DATUM / DATE : 2007-11-01

I Temperaturanstieg / Temperature rise curve :



Freigabe erteilt / general release:	Kunde / customer			
Datum / date	Unterschrift / signature			
	Würth Elektronik			
Geprüft / checked	Kontrolliert / approved	Name	Änderung / modification	Datum / date
		ME	Ver 6	2007-10-01
		RST	Version 5	2006-06-02
		ME	Version 4	2005-04-18
		MST	Version 3	2004-10-11
		SST	Version 2	2004-02-02
		JH	Version 1	2000-12-06

Würth Elektronik eiSos GmbH & Co. KG

D-74638 Waldenburg · Max-Eyth-Strasse 1 - 3 · Germany · Telefon (+49) (0) 7942 - 945 - 0 · Telefax (+49) (0) 7942 - 945 - 400
<http://www.we-online.com>

Spezifikation für Freigabe / specification for release

Kunde / customer :

Artikelnummer / part number : **744324033**

LF




Bezeichnung : **SPEICHERDROSSEL WE-HC**

description : **POWER-CHOKER WE-HC**

WÜRTH ELEKTRONIK



DATUM / DATE : 2007-11-01

J Rollenspezifikation / tape and reel specification :




Gurtspezifikation / Tape specification:

A	10,85 ± 0,1	mm
B	16,0 ± 0,1	mm
C	1,50 <small>+0,1 -0,0</small>	mm
D	1,50 <small>+0,1 -0,0</small>	mm
E	4,00 ± 0,1	mm
F	2,00 ± 0,1	mm
G	1,75 ± 0,1	mm
H	11,5 ± 0,1	mm
I	11,65 ± 0,1	mm
J	4,30 ± 0,1	mm
T	0,35 ± 0,05	mm
W	24,0 ± 0,3	mm



Rollenspezifikation / Reel specification:

a	330,0 ± 0,5	mm
b	20,20 ± 0,1	mm
c	13,00 <small>+0,5 -1,0</small>	mm
d	100,0 ± 1,0	mm



The Force for tearing off cover tape is 20 to 70 grams in arrow direction

Freigabe erteilt / general release:	Kunde / customer		
Datum / date	Unterschrift / signature		
	Würth Elektronik		
Geprüft / checked	Kontrolliert / approved		
Name		Änderung / modification	Datum / date
ME	Ver 6	07-10-01	
RST	Version 5	06-06-02	
ME	Version 4	05-04-18	
MST	Version 3	04-10-11	
SST	Version 2	04-02-02	
JH	Version 1	00-12-06	

This electronic component has been designed and developed for usage in general electronic equipment. Before incorporating this component into any equipment where higher safety and reliability is especially required or if there is the possibility of direct damage or injury to human body, for example in the range of aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc, Würth Elektronik eiSos GmbH must be informed before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electrical circuits that require high safety and reliability functions or performance.

Würth Elektronik eiSos GmbH & Co. KG

D-74638 Waldenburg · Max-Eyth-Strasse 1 · 3 · Germany · Telefon (+49) (0) 7942 - 945 - 0 · Telefax (+49) (0) 7942 - 945 - 400
http://www.we-online.com