

---

Item no.: 280-641  
Product description: 3-CONDUCTOR THROUGH TERMINAL BLOCK

---



Produkt kann von Bild abweichen / product may differ

Packing unit 100 pieces

RoHS compliant

Product group	1 (Rail Mounted Terminal Blocks)
Cross section [mm <sup>2</sup> ]	0.08 - 2.5 mm <sup>2</sup>
Cross section [AWG]	28 - 12 AWG
Connection method	CAGE CLAMP® CONNECTION
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	24 A
Weight	6.68 g
Color	gray
Wiring type	Angled Type
No. of connection Points	3
No. of potentials	1
Height	36.5 mm
Height	1.44 in
Width	5 mm
Width	0.197 in
Depth	50.5 mm
Depth	1.99 in

Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in
Mounting	TS 35



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
280-641	ABS	05-HG476175/3-PDA	800	24	2,5
280-641	BV	07436/Co	800	24	2,5
280-641	CCA	NL5855	800		2,5
280-641	DNV	E-10423	800	20	2,5
280-641	GL	17295-00HH	800	24	2,5
280-641	KEMA	2082859.07	800		2,5
280-641	LR	91/20112(E6)	800	24	2,5
280-641	PRS	TE/1718/880590/08	800		2,5
280-641	RMR	11130002	800	24	2,5
280-641	UR	E45172	600	20	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected