

SAIS-M23-12P-ST-5,0M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Sensor/actuator cables are used for wiring sensors and actuators and for transmitting data or power in various applications. The moulded cable offers connected and tested connection of the plug-in connector to the cable ex-works. The cables may be exposed to a wide range of conditions, such as humidity, dust, heat, cold, shock or vibration.

The M23 cables offer: high mating frequency, high current carrying capacity and high-density contacts coupled with minimal dimensions.

Is there something you have not managed to find or you feel needs explanation? Talk to us!

General ordering data

Type	SAIS-M23-12P-ST-5,0M
Order No.	1906280500
Version	Sensor/actuator line, One end without connector, M23, No. of poles: 12, 5 m, pin, straight, shielded: No, LED: No, Sheath material: PUR, Halogen: No
GTIN (EAN)	4032248528806
Qty.	1 pc(s).

SAIS-M23-12P-ST-5,0M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 681 g

Technical specifications for cable

No. of poles	12	Wire cross section	3 x 0.75 mm ² + 8 x 0.34 mm ²
shielded	No	Insulation	TPM
Colour coding	White, Green, Yellow, Grey, Pink, Red, Black, Violet, Blue, Brown, green / yellow	Sheath material	PUR
Sheathing colour	Black	Outer diameter	7.7 ± 0.3 mm
Cable length	5 m	Temperature range, moving, min.	-5 °C
Temperature range, moving, max.	80 °C	Temperature range, stationary, min.	-40 °C
Temperature range, stationary, max.	80 °C	Halogen	No
Suitable for cable carriers	Yes	Torsion resistance	0 °/m
Bending radius, min., moving	10 x cable diameter	Bending cycles	2 Mio
Resistant to welding beads	No		

General technical data

Version	pin, straight	Contact tube diameter	M23
Housing main material	PUR	Threaded ring material	Diecast zinc
Protection degree	IP 67	Contact surface	Gold-plated
LED	No	Rated voltage	150 V
Rated current	8 A	Insulation resistance	10 ¹² Ω
Temperature range of housing	-40...+125 °C	Tightening torque	M23: 2.5 Nm
Pollution severity	2	jumpered	No

Classifications

ETIM 2.0	EC000304	ETIM 3.0	EC001855
UNSPSC	26-12-16-13	eClass 4.1	27-06-00-00
eClass 5.1	27-06-91-90	eClass 6.2	27-06-91-90
eClass 7.1	27-06-91-90		

Approvals

Approvals	
ROHS	Conform

SAIS-M23-12P-ST-5,0M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings