

.080 (2.00) Insulated Standard: Small Handle (Solder or Crimp)

SPECIFICATIONS

Contact: Brass per QQ-B-626D

Finish: Nickel


Insulated Handle: Nylon 6/6 per ASTM D4066

RATINGS

Current: 10 amps

Breakdown Voltage: 3500 VRMS minimum†

Contact Resistance: 0.010 ohms maximum



| NICKEL PLATING | |
|--|---------------------------------|
| SOLDER TYPE UP TO 16 GAUGE PART NO. | CRIMP TYPE 16 GAUGE COLOR |
| 105-0771-001 | White |
| 105-0772-001 | Red |
| 105-0773-001 | Black |

For Standard Test Jack: .080 (2.00) Diameter
FEATURES:

- Solder or crimp type connection
- Accepts wire sizes up to 16 gauge
- Nylon UL approved for self extinguishing
- Designed for use with horizontal and vertical test jacks only

See page xxx for crimp tool.

†Avoid user injury due to misapplication. See safety advisory definitions inside front cover.

