

TLS 2200® Wire & Cable Materials:

B-321 Heat-Shrinkable Polyolefin Wire Marking Sleeves

Color: White Finish: Matte

Dot matrix printable wire and cable heat shrinkable sleeve. Excellent resistance to oil and solvents.

Performance Attributes: 




Figure 36



Diagram	Part Number	B-#	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Wire Gauge	Labels Per Row	Labels Per Pkg	Rec. Ribbon
Fig. 36	PTS-0.45-350-321	B-321	Polyolefin	White	0.450 (11.4)	0.350 (8.9)	16 to 10	1	500	R6210
Fig. 36	PTS-0.45-500-321	B-321	Polyolefin	White	0.450 (11.4)	0.500 (12.7)	10 to 8	1	500	R6210
Fig. 36	PTS-0.95-1000-321	B-321	Polyolefin	White	0.950 (24.1)	1.000 (25.4)	1 to 00	1	250	R6210
Fig. 36	PTS-0.95-350-321	B-321	Polyolefin	White	0.950 (24.1)	0.350 (8.9)	16 to 10	1	500	R6210
Fig. 36	PTS-0.95-500-321	B-321	Polyolefin	White	0.950 (24.1)	0.500 (12.7)	10 to 8	1	500	R6210
Fig. 36	PTS-0.95-750-321	B-321	Polyolefin	White	0.950 (24.1)	0.750 (19.1)	4 to 2	1	250	R6210
Fig. 36	PTS-1.90-1000-321	B-321	Polyolefin	White	1.900 (48.3)	1.000 (25.4)	1 to 00	1	250	R6210
Fig. 36	PTS-1.90-350-321	B-321	Polyolefin	White	1.900 (48.3)	0.350 (8.9)	16 to 10	1	500	R6210
Fig. 36	PTS-1.90-500-321	B-321	Polyolefin	White	1.900 (48.3)	0.500 (12.7)	10 to 8	1	500	R6210
Fig. 36	PTS-1.90-750-321	B-321	Polyolefin	White	1.900 (48.3)	0.750 (19.1)	4 to 2	1	250	R6210

TLS 2200® Wire & Cable Materials:

B-390 DuraSleeve® Polypropylene Wire Marker Inserts

Color: White Finish: Matte

Designed to be printed and affixed to a wire using extruded, clear PVC Brady Wire Marking carriers.

Performance Attributes: 




Figure 38



Diagram	Part Number	B-#	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Labels Per Row	Labels Per Pkg	Rec. Ribbon
Fig. 38	BPTDS-15-390	B-390	Polypropylene	White	0.590 (15.0)	0.163 (4.1)	1	3000	R6010
Fig. 38	PTDS-15-390	B-390	Polypropylene	White	0.590 (15.0)	0.163 (4.1)	1	300	R6010
Fig. 38	BPTDS-30-390	B-390	Polypropylene	White	1.181 (30.0)	0.163 (4.1)	1	3000	R6010
Fig. 38	PTDS-30-390	B-390	Polypropylene	White	1.181 (30.0)	0.163 (4.1)	1	300	R6010

TLS 2200® Wire & Cable Materials:

B-412 Polypropylene Tag Material

Color: White Finish: Matte

Thick polypropylene material for hardware identification. High print legibility and high tensile strength.

Performance Attributes: 




Figure 28




Figure 55



Diagram	Part Number	B-#	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Labels Per Row	Labels Per Pkg	Rec. Ribbon
Fig. 28	PTL-55-412	B-412	Polypropylene	White	0.230 (5.8)	50 ft. (15.2 m)	1	1 Roll Cont.	R6210
Fig. 28	PTL-56-412	B-412	Polypropylene	White	0.375 (9.5)	50 ft. (15.2 m)	1	1 Roll Cont.	R6210
Fig. 28	PTL-57-412	B-412	Polypropylene	White	0.500 (12.7)	50 ft. (15.2 m)	1	1 Roll Cont.	R6210
Fig. 28	PTL-58-412	B-412	Polypropylene	White	0.535 (13.6)	50 ft. (15.2 m)	1	1 Roll Cont.	R6210
Fig. 28	PTL-59-412	B-412	Polypropylene	White	0.785 (19.9)	50 ft. (15.2 m)	1	1 Roll Cont.	R6210
Fig. 55	PTL-40-412	B-412	Polypropylene	White	1.938 (49.2)	0.375 (9.5)	1	750	R6210
Fig. 55	BPTL-40-412	B-412	Polypropylene	White	1.938 (49.2)	0.375 (9.5)	1	5000	R6210

TLS 2200® Wire & Cable Materials:

B-425 Polypropylene Material

Color: White Finish: Matte

White polypropylene material with matte/opaque finish for thermal transfer printing or write-on applications. Excellent solvent resistance and print performance; not recommended for long-term outdoor use.

Performance Attributes: 




Figure 47




Figure 48



Diagram	Part Number	B-#	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Labels Per Row	Labels Per Pkg	Rec. Ribbon
Fig. 47	PTLFP-01-425	B-425	Polypropylene	White	1.180 (30.0)	0.788 (20.0)	1	250	R6210
Fig. 48	PTLFT-01-425	B-425	Polypropylene	White	1.180 (30.0)	0.788 (20.0)	1	250	R6210
Fig. 47	PTLFP-02-425	B-425	Polypropylene	White	1.750 (44.5)	1.000 (25.4)	1	100	R6210

View the Material Brands & Attributes Guide on page 4.

TLS2200® Printer Ribbons on page 67.

Full Material Properties on page 187.