



**Part Number: AG3011-90**  
**Encapsulated Tilt Switch**  
**Product Data Sheet**

## PICTURE




## CONNECTION DIAGRAM



✓ RoHS Compliant


## OPERATION



## FEATURES

- Resistant to Ambient Environmental Conditions
- Case Material : Plastic Housing
- Construction : Thermo Resist Epoxy Encapsulated
- Mechanical Stress Resistant

## DIMENSIONS



Drawings not to scale.  
 All dimensions in inches (mm) nominal.

## SPECIFICATION

Load Rating	1 A at 6-24 VDC, 25 W at 120 VAC
Contact Resistance	3 Ohms MAX at 10°
Differential Angle	10° MAX
Operating Temperature	-37° +100°C
Lead Wire	18 AWG Neoprene Insulation

As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and the details of our full design and manufacturing service. All products are supplied to our standard conditions of sale unless otherwise agreed in writing.

Phone: (1) 973 777 6900

www.comus-intl.com

Fax: (1) 973 777 8405