

Soldering Tips - Weller

EW SERIES

COMPATIBLE STATIONS: Weller WES50, Weller WES51, Weller WD1, Weller WD2, Weller EC1201A, Weller EC1204A, Weller PES50, Weller PES51, Weller WCC101

Plato is one of the largest manufacturers of soldering tips in the world, producing tips to fit all of the most popular soldering stations. The long life and fast heat recovery of Plato soldering tips increases user effectiveness and decreases production times. All Plato soldering tips manufactured since January 2004 are tinned with Lead-Free solder.

Long Life: Using a high quality Plato soldering tip increases soldering speed and decreases the total cost of manufacture. Higher temperatures and high tin content solders, common in lead-free soldering processes, place additional strain on soldering iron tips. The long life of a Plato soldering iron tip reduces tip changes, decreasing the total number of tips used and decreasing production time.

Rapid Heat Recovery: Plato soldering tips are constructed from highly conductive premium grade copper to transmit heat to the work more quickly than other brands of soldering tips. This quick heat recovery enables more joints to be soldered per minute, thus reducing manufacturing time and costs.




- Fast heat recovering increases soldering speed
- Longer tip reduces manufacturing costs
- · Fewer tip change overs

Product Dimensions

EW-303 Screwdriver

Cross Reference: Weller ETA 1.6mm 10 units/case






EW-305 Screwdriver

Cross Reference: Weller ETB 2.4mm 10 units/case





EW-307 Screwdriver

Cross Reference: Weller ETC 3.2mm 10 units/case





EW-103 Screwdriver

Cross Reference: Weller ETD 4.8mm 10 units/case










EW-105 Screwdriver

Cross Reference: Weller ETE 5.6mm 10 units/case



EW-0574 SMD flow tip

Cross Reference: Weller ETGW 5.0mm 10 units/case



EW-301 Screwdriver

Cross Reference: Weller ETH



EW-302 Screwdriver, long

Cross Reference: Weller ETJ 0.8mm 10 units/case



EW-304 Screwdriver, long

Cross Reference: Weller ETK 1.2mm 10 units/case



EW-306 Screwdriver, long

Cross Reference: Weller ETL 2.0mm 10 units/case



EW-308 Screwdriver, long

Cross Reference: Weller ETM 3.2mm



EW-404 Conical, long

Cross Reference: Weller ETO 0.8mm 10 units/case







EW-403 Conical

Cross Reference: Weller ETP 0.8mm 10 units/case






EW-101 Screwdriver, micro

Cross Reference: Weller ETR 1.8mm 10 units/case





EW-4796 Point

0.3mm 10 units/case



EW-402 Conical, long

Cross Reference: Weller ETS 0.4mm 10 units/case



EW-401 Conical

Cross Reference: Weller ETT 0.6mm 10 units/case






EW-511 Bevel

Cross Reference: Weller ETV 0.8mm 10 units/case





EW-0602 Angled SMD


0.5x0.8mm 10 units/case



EW-513 Bevel

Cross Reference: Weller ETAA 1.8mm 10 units/case










EW-515 Bevel

Cross Reference: Weller ETBB 2.4mm 10 units/case



3.2mm 10 units/case









Environmental Policy

Techspray is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Resources

Techspray products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

North America

Techspray P.O. Box 949 Amarillo, TX 79105 800-858-4043

Email: tsales@techspray.com

<u>Europe</u>

ITW Contamination Control Saffierlaan 5 2132 VZ Hoofddorp The Netherlands +31 88 1307 400 Email: info@itw-cc.com Countries Outside US

Call to locate a distributor in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.

© 2013 Techspray, A Division of ITW

