

PLUGBORD™ PART NO. : 838WE



Description :

4.5" X 6.5" X 0.062, Hole Dia.: 0.062" Positioned at alternating intersection of 0.10" grid
Plated Contacts Only

Design for mounting transistors

44 edge contacts: 22 per side on 0.156" centers tin alloy plated.

Unrestricted component placement over entire board surface

Circuit Pattern :	Plated Contacts Only
Contacts :	22/44 @ 0.156" Centers tin alloy plated
16 Pin DIP Capacity :	N/A
Hole Diameter :	0.062" { 1.5748 mm }
Grid :	Alternating intersection of 0.10" grid as " G " Pattern
Dimension { H, W, T } :	4.5" X 6.5" X 0.062"
Material :	FR4 Epoxy Glass { MIL - P13949 type Gf }
Wire-Wrap Terminals :	T125, T126
Solder Connector :	R644
Wire-Wrap Socket Pins :	R32
Wire-Wrap Connector :	R644-3
Extender :	3690
NEMA Grade :	FR4
UL Flammability Class :	94V - 0

