# **Immerse Tin Powder**

600-020 90 grams for 1 litre / 600-021 - 450 grams for 5 litres

## **Description**

A powder for making an immerse tin solution for plating a smooth even surface of tin on copper circuits at room temperature. A tin plated circuit protects the circuit from oxidisation and greatly improves solderability.

# **Mixing**

Although used at room temperature, the powder must be dissolved with hot (50°C-60°C) distilled water.

If using the 600-020 90g for 1 litre put 0.25 litres of cold water into the bottle and then fill to the top with nearly boiling water from a kettle. Screw the cap back on tightly and then shake vigorously. Leave for 5 minutes and then shake again.

If the 600-021- 450grams for 5 litres mix is being used, this should be dissolved in hot water (50-60°C) to a clean plastic container. This can then be used as above or poured into one of our heated process tanks.

Alternatively the tin can be mixed in our process tanks by firstly filling them  $\frac{3}{4}$  full with deionised/distilled water, then switching on the heater and heating to  $50\text{-}60^{\circ}\text{C}$  in our process tanks with adjustable temperature controller. If using our Bench Lines the tinning tank is pre-set to  $50^{\circ}\text{C}$ 

When the water is up to temperature, slowly add the tin powder stirring continuously taking care not to damage the silica glass heater.

When the power is all mixed in, switch off the heater and allow the solution to cool down to room temperature. It is now ready to be used and for best results should always be used at this temperature. In the case of Bench Lines the heater need only be turned on to warm the solution to 20°C if necessary, and then turned off again.

# **Usage**

Firstly it is important that the copper is perfectly clean and free from oxidisation. After the photoresist has been stripped from the circuit and it has been washed and dried it should be scrubbed clean with a PC182 scrubbing block (part no. 900-009). Then bang the board and rub with a hard clean cloth to remove any particles left by the scrubbing block and immediately immerse in the tin.

With fresh solution, after 20 seconds a coating of 0.2 microns will be plated,

0.8-1.0 microns after 5 minutes and 4-5 microns after 3 hours. When the initial area of copper has been plated the tin will begin to plate tin on tin. It is therefore uneconomical to leave a board immersed for too long, overnight for instance.

For optimum results the board should be immersed in cold water as soon as it is removed from the tin. This will stop the tinning process, the board should then be washed in hot water (40°C+) and rubbed dry with a clean cloth before air drying with a hair dryer or other hot air blower.

# **Capacity and Shelf Life**

1 litre of fresh solution will plate 30-40 complete copper Eurocards with 1-1.5 microns of tin or 10 Eurocards with 5 microns. As an average etched circuit has 30% copper a figure of 100-135 Eurocards respectively is a more accurate figure. The solution will have up to six months shelf life if used in a Mega process tank.

# **Health and Safety**

Full health and safety details are on the rear of this instruction sheet. A report by an occupational hygienist concluded that, under the test conditions, NO LOCAL EXHAUST VENTILATION IS REQUIRED using this tin in Mega's processing tanks. A copy of the report is available upon request.

### **Associated Products**

A range of associated products for use with this tin are detailed in our free product catalogue. Please telephone us for your copy, view or download via our web site: www.megauk.com

### Manufacturer

Kepets GmbH Nordstrasse 24, S-35641, Schoeffengrund 2, Laufdorf Germany, Tel: +49 644 55023



# Mega Electronics Ltd.,

Mega House, Grip Industrial Estate, Linton, Cambridge, CB21 4XN Tel: +44 (0) 1223 893900 Fax +44 (0) 1223 893894 email: sales@megauk.com web: www.megauk.com

#### SECTION 1 PRODUCT IDENTIFICATION AND MANUFACTURE

NAME: MEGA: PC168 IMMERSE TIN PART NO: 600-020 & 600-021

MANUFACTURER'S/SUPPLIERS NAME, REGISTERED ADDRESS AND **EMERGENCY TEL NO:** 

MEGA ELECTRONICS LTD THE GRIP INDUSTRIAL ESTATE LINTON CAMBRIDGE CB21 4XN TEL NO: +44 (0) 1223 893900

#### ORGANISATIONS NAME & ADDRESS AT WHICH MANUFACTURED:

KEPETS GmbH NORDSTR 24 D35641 SCHOFFENGRUND TEL NO: (0049) 6445 5023/4

#### SECTION 2 COMPOSITION/INFORMATION ON INGREDIENTS

COMPONENT %BY WT CAS & EEC Nos: HAZARD R PHRASE NOS: **THIOUREA** 27 62-56-6 R22 & R40 Xn 200-543-5 STANNOUS 15 7772-99-8 CHLORIDE EEC: NCC

#### **SECTION 3 HAZARDS IDENTIFICATION**

HARMFUL. HAZARDOUS TO HEALTH IF SWALLOWED. INORGANIC SUBSTANCE. AVOID ENTRY INTO DRAINAGE SYSTEM

#### SECTION 4 FIRST AID MEASURES

INHALATION: REMOVE FROM EXPOSURE TO FRESH AIR.

SKIN CONTACT: WASH IMMEDIATELY WITH PLENTY OF WATER

EYE CONTACT: IRRIGATE THOROUGHLY WITH WATER. SEEK MEDICAL ADVICE.

INGESTION: WASH OUT MOUTH THOROUGHLY WITH WATER AND GIVE WATER TO

MEDICAL NOTES:

#### **SECTION 5 FIRE FIGHTING MEASURES**

EXTINGUISHING MEDIA

WATER SPRAY, FOAM, DRY POWDER, CO2.

**COMBUSTION PRODUCTS** 

SO2 RELEASED IN CASE OF FIRE.

FIRE/EXPLOSION SCENARIOS

SPECIAL PROTECTIVE EQUIPMENT FOR FIRE FIGHTERS: NONE

### **SECTION 6 ACCIDENTAL RELEASE MEASURES**

PERSONAL PROTECTION

WEAR RESPIRATORY PROTECTION. PREVENT SKIN AND EYE CONTACT.

**ENVIRONMENTAL PRECAUTIONS** 

PREVENT ENTRY INTO DRAINAGE SYSTEM

WORKPLACE PRECAUTIONS

DO NOT EAT, DRINK OR SMOKE.

METHODS FOR CLEARING UP
DRY: COLLECT AND PUT INTO SUITABLE CONTAINER FOR DISPOSAL. LIQUID:
ABSORB IN SAND OR OTHER INERT MATERIAL AND PUT INTO SUITABLE CONTAINER FOR DISPOSAL

#### SECTION 7 HANDLING AND STORAGE

HANDLING PRECAUTIONS

HARMFUL IF SWALLOWED. ALWAYS WEAR SUITABLE PROTECTIVE CLOTHING. NO LOCAL EXHAUST VENTILATION IS REQUIRED.

STORAGE INCLUDING ANY SPECIAL REQUIREMENTS (TEMPERATURE.

STORE ONLY IN SUITABLE POLYETHYLENE CONTAINERS ENSURING THEY ARE TIGHTLY CLOSED. STORE AT ROOM TEMPERATURE. KEEP FROM FREEZING WHEN MIXED. NO LOCAL EXHAUST VENTILATION REQUIRED.

#### SECTION 8 EXPOSURE CONTROL/PERSONAL PROTECTION

**ENGINEERING CONTROLS/VENTILATION** 

NO LOCAL EXHAUST VENTILATION REQUIRED IF USED ACCORDING TO INSTRUCTIONS.

RESPIRATORY PROTECTION

PROTECTIVE MASK REQUIRED WHEN MIXING

EYE PROTECTION

WEAR SAFETY GLASSES.

HAND PROTECTION

WEAR RUBBER GLOVES

### SKIN PROTECTION

ALWAYS OBSERVE ALL LISUAL PRECAUTIONS WHEN HANDLING CHEMICALS. DO NOT EAT, DRINK OR SMOKE WHEN HANDLING.

#### **SECTION 9 PHYSICAL AND CHEMICAL PROPERTIES**

APPEARANCE: POWDER (SOLID) COLOUR: WHITE TO LIGHT BROWN

**ODOUR**: WEAK OF HYDROGEN SULPHIDE

ACIDITY/ALKALINITY pH: 1.5 AT 20°C (90gr/Ltr) (H20)

BOILING POINT®C MELTING POINT °C:

FLASH POINT °C (Open/Closed Cup): AUTOIGNITION TEMP °C:

THERMAL DECOMPOSITION TEMP °C:

OXIDISING PROPERTIES:

**EXPLOSIVE PROPERTIES:** 

EXPLOSIVE LIMITS AT 25°C (% VOL IN AIR)

LOWER: UPPER:

RELATIVE DENSITY: 0.87g/cm<sup>3</sup> SOLID CONTENT %:

SOLUBILITY IN WATER: At 20°C 100g/LITRE SOLUBILITY IN ORGANIC SOLVENTS:

WATER AT 20°C 100g/LITRE WATER AT 60°C 220gLITRE

**VOLATILE CONTENT %:** 

VAPOUR PRESSURE mmHg at 20°C RELATIVE VAPOUR DENSITY (air = 1): (of principle component and name):

**EVAPORATION RATE** CONDUCTIVITY:

### **SECTION 10 STABILITY AND REACTIVITY PROPERTIES**

CONDITIONS TO AVOID:

MATERIALS TO AVOID: ALKALINE SOLUTIONS

HAZARDOUS DECOMPOSITION PRODUCTS:

IN CASE OF FIRE SO2.

HAZARDOUS POLYMERISATION - MAY/WILL/NOT occur - State condition to avoid

WILL NOT OCCUR

#### **SECTION 11 TOXICOLOGICAL INFORMATION**

EFFECT OF EYE CONTACT: IRRITATING EFFECT, NO ACUTE TOXICITY.

EFFECT OF SKIN CONTACT: IRRITATING EFFECT, NO ACUTE TOXICITY.

EFFECT OF INHALATION: IRRITATING EFFECT, NO ACUTE TOXICITY.

EFFECT OF INGESTION: HARMFUL EFFECT

Any known data on sensitisation carcinogenicity, mutagenicity, teratogenicity, or narcosis. THIOUREA IS CURRENTLY ON THE SUSPECTED CARCINOGEN LIST. IRREVERSIBLE EFFECTS ARE POSSIBLE.

### **SECTION 12 ECOLOGICAL INFORMATION**

NO ACUTE TOXICITY BUT AVOID ENTRY INTO DRAINAGE SYSTEM/GROUND. INORGANIC SUBSTANCE

#### **SECTION 13 DISPOSAL CONSIDERATIONS**

SOLUTIONS AND UNUSED POWDERS SHOULD BE DISPOSED OF ACCORDING TO AL GOVERNMENT REGULATIONS VIA AUTHORISED WASTE DISPOSAL AGENCIES. TREAT AS WEAK ACID.

#### SECTION 14 TRANSPORT INFORMATION

UN-Nr: 2811 IATA CLASS: 6.1 PACKING GROUP: III

### **SECTION 15 REGULATORY INFORMATION**

PRODUCT LABEL DETAILS - PER CHIP REGULATION 9

PRODUCT TRADE NAME/DESIGNATION: IMMERSE TIN POWDER

CONTAINS: THIOUREA.

HAZARD SYMBOL: Xn

RISK PHRASE NOS & WORDS:

R22 HARMFUL IF SWALLOWED. R40 POSSIBLE RISK OF IRREVERSIBLE EFFECTS.

SAFETY PHRASE NOS & WORDS:

\$22 DO NOT BREATHE DUST. \$41 IN CASE OF FIRE AND/OR EXPLOSION DO NOT BREATHE FUMES. \$24/25 AVOID CONTACT WITH SKIN AND EYES. \$36 WEAR SUITABLE PROTECTIVE CLOTHING. \$26 IN CASE OF CONTACT WITH EYES, RINSE IMMEDIATELY AND SEEK MEDICAL ADVICE. \$28 AFTER CONTACT WITH SKIN, WASH IMMEDIATELY WITH PLENTY OF SOAP AND WATER

The information and recommendations contained herein are believed to be accurate -However no guarantee or warranty expressed or implied is given