


# Multicore Arctic Grade



## Specification Table:

Arctic Grade Cable	3 × 0.75mm <sup>2</sup>	3 × 1.5mm <sup>2</sup>	3 × 2.5mm <sup>2</sup>
Product Reference	CU / PVC / PVC		
Voltage Rating	300 / 500V		
Conductor Size	0.75mm <sup>2</sup> (Class 5 )	1.5mm <sup>2</sup> (Class 5 )	2.5mm <sup>2</sup> (Class 5 )
Conductor Resistance	Max, 26W/KM at 20 °C	Max, 13.3W/KM at 20 °C	Max, 7.98W/KM at 20 °C
Insulation Material	Arctic Grade PVC (-20 °C)		
Sheath Colour	Yellow		
Insulation Radial Thickness	0.6mm (Average)	0.7mm (Average)	0.8mm (Average)
Core Identification	Green/Yellow-Blue-Brown		
Lay Up	Right Hand Lay		
Sheath Material	Arctic Grade PVC (-20 °C)		
Sheath Radial Thickness	0.8mm Average	0.9mm Average	1.1mm Average
Over-Sheath Diameter	6.7mm (Approximately)	8.2mm (Approximately)	10mm (Approximately)
Cable Weight	66kg/km (Approximately)	106kg/km (Approximately)	162kg/km (Approximately)
Sheath Embossing	3183YAG Arctic Grade 3 × 0.75mm <sup>2</sup> 300/500V	3183YAG Arctic Grade 3 × 1.5mm <sup>2</sup> 300/500V	3183YAG Arctic Grade 3 × 2.5mm <sup>2</sup> 300/500V



## Specification Table:

Arctic Grade Cable	3 × 0.75mm <sup>2</sup>	3 × 1.5mm <sup>2</sup>	3 × 2.5mm <sup>2</sup>
Product Reference	CU / PVC / PVC		
Voltage Rating	300 / 500V		
Conductor Size	0.75mm <sup>2</sup> (Class 5 )	1.5mm <sup>2</sup> (Class 5 )	2.5mm <sup>2</sup> (Class 5 )
Conductor Resistance	Max, 26W/KM at 20 °C	Max, 13.3W/KM at 20 °C	Max, 7.98W/KM at 20 °C
Insulation Material	Arctic Grade PVC (-20 °C)		
Sheath Colour	Blue		
Insulation Radial Thickness	0.6mm (Average)	0.7mm (Average)	0.8mm (Average)
Core Identification	Green/Yellow-Blue-Brown		
Lay Up	Right Hand Lay		
Sheath Material	Arctic Grade PVC (-20 °C)		
Sheath Radial Thickness	0.8mm Average	0.9mm Average	1.1mm Average

# Multicore Arctic Grade



Arctic Grade Cable	3 × 0.75mm <sup>2</sup>	3 × 1.5mm <sup>2</sup>	3 × 2.5mm <sup>2</sup>
Over-Sheath Diameter	6.7mm (Approximately)	8.2mm (Approximately)	10mm (Approximately)
Cable Weight	66 kg/km (Approximately)	106kg/km (Approximately)	162 kg/km (Approximately)
Sheath Embossing	3183YAG Arctic Grade 3 × 0.75mm <sup>2</sup> 300/500V	3183YAG Arctic Grade 3 × 1.5mm <sup>2</sup> 300/500V	3183YAG Arctic Grade 3 × 2.5mm <sup>2</sup> 300/500V



## Specification Table:

Arctic Grade Cable	3 × 1.5mm <sup>2</sup>	3 × 2.5mm <sup>2</sup>
Product Reference	CU / PVC / PVC	
Voltage Rating	300 / 500V	
Conductor Size	1.5mm <sup>2</sup> (Class 5 )	2.5mm <sup>2</sup> (Class 5 )
Conductor Resistance	Max, 13.3W/KM at 20 °C	Max, 7.98W/KM at 20 °C
Insulation Material	Arctic Grade PVC (-20 °C)	
Sheath Colour	Orange	
Insulation Radial Thickness	0.7mm (Average)	0.8mm (Average)
Core Identification	Green/Yellow-Blue-Brown	
Lay Up	Right Hand Lay	
Sheath Material	Arctic Grade PVC (-20 °C)	
Sheath Radial Thickness	0.9mm Average	1.1mm Average
Over-Sheath Diameter	8.2mm (Approximately)	10mm (Approximately)
Cable Weight	106kg/km (Approximately)	162kg/km (Approximately)
Sheath Embossing	3183YAG Arctic Grade 3 × 1.5mm <sup>2</sup> 300/500V	3183YAG Arctic Grade 3 × 2.5mm <sup>2</sup> 300/500V

## Part Number Table

Description	Part Number
Multicore, Arctic, 3,0.75mm <sup>2</sup> ,Yellow,100M	5095
Multicore, Arctic, 3, 0.75mm <sup>2</sup> , Blue,100M	5096
Multicore, Arctic, 3, 1.5mm <sup>2</sup> ,Yellow,100M	5097
Multicore, Arctic, 3, 1.5mm <sup>2</sup> ,Orange,100M	5098
Multicore, Arctic, 3, 1.5mm <sup>2</sup> , Blue, 100M	5099
Multicore, Arctic, 3, 2.5mm <sup>2</sup> ,Yellow,100M	5100
Multicore, Arctic, 3, 2.5mm <sup>2</sup> , Blue, 100M	5101
Multicore, Arctic, 3, 2.5mm <sup>2</sup> ,Orange,100M	5102

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.