

AN-2031 LMZ12003 3A Demo Board SIMPLE SWITCHER® Power Module Quick Start Guide

1 Description

The LMZ12003 SIMPLE SWITCHER power module is a complete, easy to use step-down DC-DC solution capable of driving up to 3A load The LMZ12003 is available in an innovative, easy to use package that enhances thermal performance and allows for hand or machine soldering.

The LMZ12003 demo board can accept an input voltage rail between 4.5V and 20V and deliver an adjustable and highly accurate output voltage as low as 0.8V. The LMZ12003 only requires three external resistors and four external capacitors to complete the power solution. The LMZ12003 is a reliable and robust solution with the following protection features: thermal shutdown, input under-voltage lockout (UVLO), output over-voltage protection (OVP), short-circuit protection, output current limit, and allows startup into a pre-biased output. A single resistor adjusts switching frequency up to 1 MHz.

2 **Packaging Highlights**

- 7 lead module package (Similar to TO-263)
- Single exposed die attach pad for enhanced thermal performance ٠
- 10.2 x 13.8 x 4.6 mm module package
- High power density
- 1.7" x 2.3" reduced size demo board form factor

3 **Demo Board Features**

- Power input voltage range 4.5V-20V ٠
- UVLO programmed at 4.5V
- Adjustable output voltage range 0.8V to 6V
- Up to 3A output current
- Integrated shielded inductor in module
- Efficiency up to 92% ٠
- All ceramic capacitor design
- No loop compensation required
- Starts into pre-biased loads
- Short circuit protection
- Thermal shutdown
- Only 9 external passives plus module
- 2 layer low cost assembly

SIMPLE SWITCHER is a registered trademark of Texas Instruments. All other trademarks are the property of their respective owners.



www.ti.com

Typical Applications

4 **Typical Applications**

- Point of load conversions from 5V and 12V input rails •
- Space constrained applications •
- Industrial controls .
- Telecom
- Networking equipment



Figure 1. Front View

Copyright © 2010–2013, Texas Instruments Incorporated



www.ti.com



Figure 2. Back View

Table 1. Absolute Maximum Module Ratings

VIN, RON to GND	-0.3V to 25V
EN, FB, SS to GND	-0.3V to 7V

Table 2. Module Operating Ratings

VIN	4.5V to 20V
EN (Input on pin 3 module pin)	0V to 6.5V
Junction Temperature Range (Tj)	- 40C to +125C

Table 3. Demo Board Operating Ratings

VIN	4.5V to 20V
VOUT (Default setting)	1.8V
IOUT	0A to 3A
EN (Input on demo board post)	0V to 20V
UVLO setting on ENable input	4.5V
Soft-start time	2.2 mSec
Operating Temperature Range (Tj)	- 40C to +70C (at full 3A load)

3



Demo Board Schematic

www.ti.com

5 Demo Board Schematic



6 Demo Board Bill of Materials (BOM)

Table 4. Board Bill of Materials (BOM)

Ref Des	Description	Case	Manufacturer Part Number
Ron	32.4 kohm 1% resistor	603	
Rent	32.4 kohm 1% resistor	603	
Renb	11.8 kohm 1% resistor	603	
Rfbt	1.87 kohm 1% resistor	603	
Rfbb	1.50 kohm 1% resistor	603	
Cff	0.022 uF 50V X7R ceramic capacitor	603	
Css	0.022 uF 50V X7R ceramic capacitor	603	
Cin	10 uF 50V X5R ceramic capacitor	1210	UMK325BJ106MM-T
Cout1	1.0 uF 50V X7R ceramic capacitor	1206	UMK316B7105KL-T
Cout2	100 uF 6.3V X5R ceramic capacitor	1210	JMK325BJ107MM-T
U1	LMZ12003 SIMPLE SWITCHER Power Module	TO-PMOD	LMZ12003TZ-ADJ

4 AN-2031 LMZ12003 3A Demo Board SIMPLE SWITCHER® Power Module Quick Start Guide

5

www.ti.com

Ref Des	Description	Case	Manufacturer Part Number	
Alternate resistor values for alternative output voltages				
VOUT	RFBT	RFBB	RON	
6	2.49k	383 Ω	124k	
5	5.62k	1.07k	100k	
3.3	3.32k	1.07k	61.9k	
2.5	2.26k	1.07k	47.5k	
1.8	1.87k	1.50k	32.4k	
1.5	1.00k	1.13k	28.0k	
1.2	4.22k	8.45k	22.6k	
0.8	0.0K	39.2k	24.9k	

Table 4. Board Bill of Materials (BOM) (continued)

7 Demo Board Hookup

VOUT Connect the load to V_{OUT} and one of the GND posts. The module can source up to a 3A load current.

Connect VIN to a positive voltage in the 4.5 to 20V range. Connect the negative terminal of the source supply to one of the posts labeled GND.

The Enable input post is configured for direct connection to the Vin post. With the chosen resistor values this results in an under voltage lockout level of 4.5V input. The top enable resistor is RENT (aka REN1) and the bottom enable resistor is RENB (aka REN2).

If the Enable post is disconnected, the module will be disabled and about 20 uA of supply current will flow from Vin to ground while in the disabled mode. With the enable input connected to Vin via the resistor divider there will be about 1.5 mA of no-load quiescent current into the Vin input. Additional current flows into the enable divider string.

8 Demo Board Passive Components

Soft-start capacitor: The soft-start capacitor controls the rise time of the output voltage when power is first applied and following the clearing of a fault mode.

Feedback divider: Regulator output voltage is programmed though the selection of the two resistors. RFBT (aka RFB1)and RFB (aka RFB2) A feed forward capacitor (CFF) is located in parallel with the upper feedback divider resistor. This capacitor improves the step response to abrupt changes in load current. For a different output voltage, see Table 4 when modifying the board. Resistor values shown will minimize error in output voltage setting.

RON Resistor: The primary function of the RON resistor is to set the On-Time interval of the internal control section switching cycle. The secondary function of the RON resistor is to create a nearly constant operating frequency over the input operating voltage range. If the output voltage of the regulator is changed by adjusting the feedback divider then it is generally required that the RON resistor value also be changed in order to maintain the same operating frequency.

Cout: A parallel connection of a 1 μ F 50V and a 100 μ F 6.3V multilayer ceramic are used for the output capacitor. Locations are provided on the PCB assembly for experimenting with additional output capacitors..

Cin: A 10 uF 50V multilayer ceramic is connected as the input filter. Locations are provided on the PCB assembly for experimenting with additional input capacitors.



6

9 Performance Characteristics



5.25

2

1.5

OUTPUT CURRENT (A)

5

3

2.5

25℃

0.5

1

1.8 L 0

IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have *not* been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

Products		Applications	
Audio	www.ti.com/audio	Automotive and Transportation	www.ti.com/automotive
Amplifiers	amplifier.ti.com	Communications and Telecom	www.ti.com/communications
Data Converters	dataconverter.ti.com	Computers and Peripherals	www.ti.com/computers
DLP® Products	www.dlp.com	Consumer Electronics	www.ti.com/consumer-apps
DSP	dsp.ti.com	Energy and Lighting	www.ti.com/energy
Clocks and Timers	www.ti.com/clocks	Industrial	www.ti.com/industrial
Interface	interface.ti.com	Medical	www.ti.com/medical
Logic	logic.ti.com	Security	www.ti.com/security
Power Mgmt	power.ti.com	Space, Avionics and Defense	www.ti.com/space-avionics-defense
Microcontrollers	microcontroller.ti.com	Video and Imaging	www.ti.com/video
RFID	www.ti-rfid.com		
OMAP Applications Processors	www.ti.com/omap	TI E2E Community	e2e.ti.com
Wireless Connectivity	www.ti.com/wirelessconr	nectivity	

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265 Copyright © 2013, Texas Instruments Incorporated