



SAFETY DATA SHEET FLEXIBLE SILICONE COATING

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product name FLEXIBLE SILICONE COATING
Product No. FSC-b, EFSC15ML, EFSC05L, ZE

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Conformal coating for appliance protection
Uses advised against At this moment in time we do not have information on use restrictions. They will be included in this safety data sheet when available

1.3. Details of the supplier of the safety data sheet

Supplier ELECTROLUBE. A division of HK
WENTWORTH LTD
ASHBY PARK, COALFIELD WAY,
ASHBY DE LA ZOUCH, LEICESTERSHIRE
LE65 1JR
UNITED KINGDOM
+44 (0)1530 419600
+44 (0)1530 416640
info@hkw.co.uk

1.4. Emergency telephone number

+44 (0)1530 419600 between 8.30am - 5.00pm Mon – Fri

SECTION 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

Classification (1999/45/EEC) Xn;R20/21. Xi;R38. R10.

Environment

The product is not expected to be hazardous to the environment.

2.2. Label elements

Contains XYLENE

Labelling



Harmful

Risk Phrases

R10	Flammable.
R20/21	Harmful by inhalation and in contact with skin.
R38	Irritating to skin.

Safety Phrases

S24	Avoid contact with skin.
S36/37	Wear suitable protective clothing and gloves.
S51	Use only in well-ventilated areas.

2.3. Other hazards

Not Classified as PBT/vPvB by current EU criteria.

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

FLEXIBLE SILICONE COATING**3.2. Mixtures**

XYLENE		30-60%
CAS-No.: 1330-20-7	EC No.: 215-535-7	
Classification (EC 1272/2008)	Classification (67/548/EEC)	
Flam. Liq. 3 - H226	R10	
Acute Tox. 4 - H312	Xn;R20/21	
Acute Tox. 4 - H332	Xi;R38	
Skin Irrit. 2 - H315		

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

Composition Comments

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels.

SECTION 4: FIRST AID MEASURES**4.1. Description of first aid measures****Inhalation**

Move the exposed person to fresh air at once. Keep the affected person warm and at rest. Get prompt medical attention.

Ingestion

DO NOT INDUCE VOMITING! Rinse mouth thoroughly. Provide rest, warmth and fresh air. Get medical attention immediately!

Skin contact

Wash the skin immediately with soap and water. Get medical attention if irritation persists after washing.

Eye contact

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Contact physician if irritation persists.

4.2. Most important symptoms and effects, both acute and delayed**4.3. Indication of any immediate medical attention and special treatment needed**

Treat symptomatically

SECTION 5: FIREFIGHTING MEASURES**5.1. Extinguishing media****Extinguishing media**

Fire can be extinguished using: Foam. Dry chemicals, sand, dolomite etc.

Unsuitable extinguishing media

Do not use water jet as an extinguisher, as this will spread the fire.

5.2. Special hazards arising from the substance or mixture**Hazardous combustion products**

Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.

Unusual Fire & Explosion Hazards

No unusual fire or explosion hazards noted.

Specific hazards

When heated and in case of fire, harmful vapours/gases may be formed.

5.3. Advice for firefighters**Special Fire Fighting Procedures**

Avoid breathing fire vapours. Cool containers exposed to flames with water until well after the fire is out.

Protective equipment for fire-fighters

Self contained breathing apparatus and full protective clothing must be worn in case of fire.

SECTION 6: ACCIDENTAL RELEASE MEASURES**6.1. Personal precautions, protective equipment and emergency procedures**

Wear protective clothing as described in Section 8 of this safety data sheet.

FLEXIBLE SILICONE COATING

6.2. Environmental precautions

Do not discharge onto the ground or into water courses.

6.3. Methods and material for containment and cleaning up

Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Absorb in vermiculite, dry sand or earth and place into containers.

6.4. Reference to other sections

Wear protective clothing as described in Section 8 of this safety data sheet. See section 11 for additional information on health hazards. For waste disposal, see section 13.

SECTION 7: HANDLING AND STORAGE

7.1. Precautions for safe handling

Avoid spilling, skin and eye contact. Keep away from heat, sparks and open flame. Provide good ventilation.

7.2. Conditions for safe storage, including any incompatibilities

Flammable/combustible - Keep away from oxidisers, heat and flames. Store in tightly closed original container in a dry, cool and well-ventilated place. Keep in original container.

7.3. Specific end use(s)

The identified uses for this product are detailed in Section 1.2.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

Name	STD	TWA - 8 Hrs		STEL - 15 Min		Notes
XYLENE	WEL	50 ppm	220 mg/m ³	100 ppm	441 mg/m ³	Sk

WEL = Workplace Exposure Limit.

Sk = Can be absorbed through skin.

8.2. Exposure controls

Protective equipment



Process conditions

Use engineering controls to reduce air contamination to permissible exposure level. Provide eyewash station.

Engineering measures

Provide adequate ventilation, including appropriate local extraction, to ensure that the defined occupational exposure limit is not exceeded.

Respiratory equipment

In case of inadequate ventilation and work of brief duration, use suitable respiratory equipment. Use respiratory equipment with combination filter, type A2/P3. EN14387

Hand protection

Protective gloves must be used if there is a risk of direct contact or splash. The most suitable glove must be chosen in consultation with the gloves supplier, who can inform about the breakthrough time of the glove material. Nitrile gloves are recommended. Gloves should conform to EN374

Eye protection

Use approved safety goggles or face shield. EN166

Other Protection

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

Hygiene measures

DO NOT SMOKE IN WORK AREA! Wash hands at the end of each work shift and before eating, smoking and using the toilet. Wash promptly with soap & water if skin becomes contaminated. Use appropriate skin cream to prevent drying of skin. When using do not eat, drink or smoke.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

FLEXIBLE SILICONE COATING

9.1. Information on basic physical and chemical properties

Appearance	Liquid
Colour	Colourless.
Solubility	Immiscible with water
Relative density	1.05 @ 20 C (68 F)
Viscosity	550 cps @ 20 C (68 F)
Flash point	25 (77 F) CC (Closed cup).

9.2. Other information

None.

SECTION 10: STABILITY AND REACTIVITY

10.1. Reactivity

No specific reactivity hazards associated with this product.

10.2. Chemical stability

Stable under normal temperature conditions.

10.3. Possibility of hazardous reactions

No information required.

Hazardous Polymerisation

Will not polymerise.

10.4. Conditions to avoid

Avoid heat. Avoid contact with oxidisers or reducing agents.

10.5. Incompatible materials

Materials To Avoid

No specific, or groups of materials are likely to react to produce a hazardous situation.

10.6. Hazardous decomposition products

Fire creates: Toxic gases/vapours/fumes of: Carbon monoxide (CO). Carbon dioxide (CO₂).

SECTION 11: TOXICOLOGICAL INFORMATION

11.1. Information on toxicological effects

Toxicological information

No data recorded.

Other Health Effects

This substance has no evidence of carcinogenic properties.

Inhalation

Harmful by inhalation. May cause irritation to the respiratory system.

Ingestion

May cause discomfort if swallowed.

Skin contact

Irritating to skin. Product has a defatting effect on skin.

Eye contact

Irritating to eyes.

Route of entry

Inhalation. Skin absorption.

Toxicological information on ingredients.

FLEXIBLE SILICONE COATING
XYLENE (CAS: 1330-20-7)

Acute toxicity:

Acute Toxicity (Oral LD50)

3523 mg/kg Rat

Acute Toxicity (Dermal LD50)

12126 mg/kg Rabbit

Acute Toxicity (Inhalation LC50)

2700 mg/l (vapours) Rabbit 4 hours

Aspiration hazard:

Inhalation

Harmful by inhalation. Upper respiratory irritation. Central nervous system depression. Vapours may cause drowsiness and dizziness.

Ingestion

Swallowing concentrated chemical may cause severe internal injury. May cause nausea, headache, dizziness and intoxication. Diarrhoea.

Skin contact

Harmful in contact with skin. Irritating to skin.

Eye contact

May cause severe irritation to eyes.

Central nervous system Liver Kidneys

SECTION 12: ECOLOGICAL INFORMATION

Ecotoxicity

Not regarded as dangerous for the environment.

Ecological information on ingredients.

XYLENE (CAS: 1330-20-7)

Ecotoxicity

The product components are not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

12.1. Toxicity

Ecological information on ingredients.

XYLENE (CAS: 1330-20-7)

Acute Toxicity - Aquatic Invertebrates

EC50 48 hours 1.0 mg/l Daphnia magna

Acute Toxicity - Aquatic Plants

IC50 72 hours 2.2 mg/l

12.2. Persistence and degradability

Degradability

There are no data on the degradability of this product.

Ecological information on ingredients.

XYLENE (CAS: 1330-20-7)

Degradability

The product is biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential

No data available on bioaccumulation.

FLEXIBLE SILICONE COATING

Ecological information on ingredients.

XYLENE (CAS: 1330-20-7)

Bioaccumulation factor

BCF 25.9

Partition coefficient

3.2

12.4. Mobility in soil

Mobility:

The product is insoluble in water.

Ecological information on ingredients.

XYLENE (CAS: 1330-20-7)

Mobility:

The product is insoluble in water.

12.5. Results of PBT and vPvB assessment

This product does not contain any PBT or vPvB substances.

Ecological information on ingredients.

XYLENE (CAS: 1330-20-7)

Not Classified as PBT/vPvB by current EU criteria.

12.6. Other adverse effects

Not determined.

Ecological information on ingredients.

XYLENE (CAS: 1330-20-7)

Not determined.

SECTION 13: DISPOSAL CONSIDERATIONS

General information

Waste is classified as hazardous waste. Disposal to licensed waste disposal site in accordance with the local Waste Disposal Authority.

13.1. Waste treatment methods

Dispose of waste and residues in accordance with local authority requirements.

SECTION 14: TRANSPORT INFORMATION

14.1. UN number

UN No. (ADR/RID/ADN)	1263
UN No. (IMDG)	1263
UN No. (ICAO)	1263

14.2. UN proper shipping name

Proper Shipping Name	CONSUMER COMMODITY
Proper Shipping Name	PAINT

14.3. Transport hazard class(es)

ADR/RID/ADN Class	3
ADR/RID/ADN Class	Class 3: Flammable liquids.
ADR Label No.	3
IMDG Class	3
ICAO Class/Division	3

Transport Labels

FLEXIBLE SILICONE COATING

**14.4. Packing group**

ADR/RID/ADN Packing group	III
IMDG Packing group	III
ICAO Packing group	III

14.5. Environmental hazards

Environmentally Hazardous Substance/Marine Pollutant

No.

14.6. Special precautions for user

EMS	F-E, S-E
Emergency Action Code	•3Y
Hazard No. (ADR)	30
Tunnel Restriction Code	(D/E)

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

No information required.

SECTION 15: REGULATORY INFORMATION

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**Uk Regulatory References**

Chemicals (Hazard Information & Packaging) Regulations.

The Control of Substances Hazardous to Health Regulations 2002 (S.I 2002 No. 2677) with amendments.

Environmental Listing

Rivers (Prevention of Pollution) Act 1961. Control of Pollution (Special Waste Regulations) Act 1980. Control of Pollution Act 1974.

Approved Code Of Practice

Classification and Labelling of Substances and Preparations Dangerous for Supply.

Guidance Notes

Workplace Exposure Limits EH40. Introduction to Local Exhaust Ventilation HS(G)37. CHIP for everyone HSG(108).

EU Legislation

System of specific information relating to Dangerous Preparations. 2001/58/EC.

Dangerous Substance Directive 67/548/EEC.

Dangerous Preparations Directive 1999/45/EC.

Commission Directive 2000/39/EC of 8 June 2000 establishing a first list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work.

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

Authorisations (Title VII Regulation 1907/2006)

No specific authorisations are noted for this product.

Restrictions (Title VIII Regulation 1907/2006)

No specific restrictions of use are noted for this product.

15.2. Chemical Safety Assessment

No chemical safety assessment has been carried out.

FLEXIBLE SILICONE COATING

SECTION 16: OTHER INFORMATION

Revision Comments

Revised in accordance with CHIP3 and EU Directives 1999/45/EC and 2001/58/EC

Issued By Helen O'Reilly
Revision Date NOVEMBER 2012
Revision 3
SDS No. 12471

Risk Phrases In Full

R10 Flammable.
R20/21 Harmful by inhalation and in contact with skin.
R38 Irritating to skin.

Hazard Statements In Full

H226 Flammable liquid and vapour.
H312 Harmful in contact with skin.
H315 Causes skin irritation.
H332 Harmful if inhaled.

Disclaimer

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.