



Mallory Sonalert Products, Inc.

Part #:

MSE14LDT8

Sales Outline Drawing

Revision:


A

Specifications:


Sound Level Category	Loud
Mode of Operation	Dual Tone 3.5 - 3.4 kHz @ 1.5 WPS
Voltage Rating	7 to 14 VDC
Frequency	3500-3400 Hz Typical
Loudness @ 1 FT	85 to 95 dB(A) Typ.
Current Draw	50mA MAX
Housing Material	Valox (UL94V-0), Color: Black
Storage Temperature	-40° to +80° C
Operating Temperature	-40° to +65° C
Weight (Typical)	4.0g
Options	Please contact factory.

Dimensions: Inches (mm)

ROHS Compliant




EMISSION HOLE
Ø .188±.005 [4.8±0.1]



.906±.005 [23±0.1]

.590±.012 [15±0.3]



NOTE A:
TERMINALS - .031" DIA. NICKEL/TIN COATED BRASS.

NOTE B:
MOUNTING- INSERT INTO PRINTED CIRCUIT BOARD AND HAND OR MACHINE SOLDER.
UNITS ARE SUITABLE FOR WAVE SOLDERING. RECOMMENDED MAXIMUM TEMPERATURE
AND TIME DURATION FOR WAVE SOLDERING IS +270°C AND 3 SECONDS RESPECTIVELY.