



Rated cross-section $\leq 1.5 \text{ mm}^2$



LM 3.5/90



Technical Data	VDE	UL	CSA
Rated voltage	V	125*	300 300
Rated current	A	12 10	10
Clamping range max.	mm ² /AWG	1.5 14	14

*Overvoltage category III / Pollution severity 3

Additional technical data see page 52



Solder pin length 3.2 mm 4.5 mm



Colour

Poles	Type	Cat. No.	Cat. No.	Qty.
2	LM 3.5/2/90	1667750000	1699670000	100
3	LM 3.5/3/90	1667770000	1699680000	100

LM1N 3.5/90



Technical Data	VDE	UL	CSA
Rated voltage	V	125*	300 300
Rated current	A	10 10	10
Clamping range max.	mm ² /AWG	1.5 14	14

*Overvoltage category III / Pollution severity 3

Additional technical data see page 52

Solder pin length 3.2 mm 4.5 mm





Colour

Poles	Type	Cat. No.	Cat. No.	Qty.
2	LM1N 3.5/2	1716710000	1747380000	100
3	LM1N 3.5/3	1716720000	1747390000	100

Attention: Customers are advised to ensure support for LM1N on the printed circuit board.

Accessories	Page
Marking	42
Fixing	-
Miscellaneous	45

LM 3.5/135



Technical Data	VDE	UL	CSA
Rated voltage	V	125*	300 300
Rated current	A	12 10	10
Clamping range max.	mm ² /AWG	1.5 14	14

*Overvoltage category III / Pollution severity 3

Additional technical data see page 52

Solder pin length 3.2 mm 4.5 mm



Colour

Poles	Type	Cat. No.	Cat. No.	Qty.
2	LM 3.5/2/135	1714980000	1715010000	100
3	LM 3.5/3/135	1715020000	1715050000	100

Rated cross-section $\leq 1.5 \text{ mm}^2$

