

**SIZE :**

40x40x10mm (1.57"x1.57"x0.39")

**CONSTRUCTION :**

Glass fiber reinforced plastic;  
Impeller and housing PBT are UL 94V-0 rating

**OPERATING TEMPERATURE :**

Ball bearing - 30°C to +75°C  
Sleeve bearing - 10°C to +70°C

**INSULATION RESISTANCE :**

10meg Ohm min. at 500 VDC  
(between frame and terminal)

**DIELECTRIC STRENGTH :**

5mA max. at 500 VAC 60Hz one minute  
(between frame and terminal)

**FUNCTION :**

frequency generator signal option

**WEIGHT :**

18 grams


## Specifications

Specifications are subject to change without notice

MODEL NO.	BEARING	RATED VOLTAGE	OPERATING VOLTAGE RANGE	RATED CURRENT	RATED INPUT POWER	SPEED R.P.M.	MAX. AIR FLOW		MAX. AIR PRESSURE		NOISE dB-A
		VDC	V	A	W		m <sup>3</sup> /min	CFM	mmH <sub>2</sub> O	IN H <sub>2</sub> O	
BP401006M	Ball	5	4.5-5.7	0.18	0.90	5000	0.18	6.48	1.87	0.07	24
SP401006M	Sleeve	5	4.5-5.7	0.18	0.90	5000	0.18	6.48	1.87	0.07	24
BP401012M	Ball	12	10.2-13.8	0.09	1.08	5000	0.18	6.48	1.87	0.07	24
SP401012M	Sleeve	12	10.2-13.8	0.09	1.08	5000	0.18	6.48	1.87	0.07	24
BP401005H	Ball	5	4.5-5.7	0.23	1.15	6500	0.22	7.70	2.40	0.09	29
SP401005H	Sleeve	5	4.5-5.7	0.23	1.15	6500	0.22	7.70	2.40	0.09	29
BP401012H	Ball	12	10.2-13.8	0.13	1.56	6500	0.22	7.70	2.40	0.09	29
SP401012H	Sleeve	12	10.2-13.8	0.13	1.56	6500	0.22	7.70	2.40	0.09	29

\* 24V is available

Dimensions (mm)



Performance Curve

