

8445 Multi-Conductor - Audio, Control and Instrumentation Cable



For more Information
please call

1-800-Belden1

**General Description:**

22 AWG stranded (7x30) tinned copper conductors, conductors cabled, PVC insulation, PVC Jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

# Conductors	AWG	Stranding	Conductor Material
5	22	7x30	TC - Tinned Copper

Total Number of Conductors: 5

Insulation**Insulation Material:**

Insulation Material	Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.279

Outer Shield**Outer Shield Material:**

Outer Shield Material
Unshielded

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.8128

Overall Cable**Overall Cabling Color Code Chart:**

Color
Black
White
Red
Green
Brown

Overall Nominal Diameter: 4.928 mm

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +80°C
UL Temperature Rating:	80°C (UL AWM Style 2576)
Bulk Cable Weight:	35.717 Kg/Km
Max. Recommended Pulling Tension:	204.617 N
Min. Bend Radius/Minor Axis:	50.800 mm

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	CMG
CEC/C(UL) Specification:	CMG

8445 Multi-Conductor - Audio, Control and Instrumentation Cable

AWM Specification:	UL Style 2576 (150 V 80°C)
---------------------------	----------------------------

CSA Specification:	FT4
---------------------------	-----

EU Directive 2011/65/EU (ROHS II):	Yes
---	-----

EU CE Mark:	Yes
--------------------	-----

EU Directive 2000/53/EC (ELV):	Yes
---------------------------------------	-----

EU Directive 2002/95/EC (RoHS):	Yes
--	-----

EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
--	------------

EU Directive 2002/96/EC (WEEE):	Yes
--	-----

EU Directive 2003/11/EC (BFR):	Yes
---------------------------------------	-----

CA Prop 65 (CJ for Wire & Cable):	Yes
--	-----

MII Order #39 (China RoHS):	Yes
------------------------------------	-----

Flame Test

UL Flame Test:	UL1685 FT4 Loading
-----------------------	--------------------

CSA Flame Test:	FT4
------------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
----------------------	----

Electrical Characteristics (Overall)**Nom. Inductance:**

Inductance (μH/m)

0.55777

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)

111.554

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

51.1836

Max. Operating Voltage - UL:

Voltage	Description
300 V RMS	CMG
150 V RMS	UL AWM Style 2576

Max. Recommended Current:

Current

2.4 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8445 060U1000	305 MT	11.340 KG	CHROME		5 #22 PVC PVC
8445 060U500	152 MT	6.124 KG	CHROME		5 #22 PVC PVC
8445 060100	30 MT	1.452 KG	CHROME		5 #22 PVC PVC
8445 0601000	305 MT	11.793 KG	CHROME	C	5 #22 PVC PVC
8445 060500	152 MT	6.124 KG	CHROME	C	5 #22 PVC PVC
8445 0605000	1,524 MT	58.967 KG	CHROME		5 #22 PVC PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 09-19-2012

© 2013 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications

8445 Multi-Conductor - Audio, Control and Instrumentation Cable

described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.