

EL217C

A two-part, room temperature curing polyurethane system

Application

- Cable joints
- Hand held tool handles
- Abrasion resistant liners

Key Properties

- Non Toxic
- Outstanding abrasion resistance
- Excellent tear resistance
- Medium viscosity
- UV resistant

Description

- Basic Two-component polyurethane system
- Resin RL217C
- Hardener HL217C

Physical Data (approx. – values)	Resin	Hardener	Mixed
Colour	Natural Black	Amber Amber	Natural Black
Specific Gravity	1.06	1.20	1.07
Viscosity (mPas) @ 25°C	6000-8000	800	5000

Cure Schedule (150ml sample)

Temperature	Working Life (minutes)	Gel Time (minutes)	Light Handling (hours)	Full Cure (hours)
RT	90	120	24	48
30°C	-	-	16	36
60°C	-	-	4	8
80°C	-	-	2	4

*RT is defined as 20-25°C

The above are typical values and will vary depending on the cured mass and application. Hotter temperatures may be used for faster cure but will result in higher post cure shrinkage and higher cure exotherm. Experimentation and testing is suggested to avoid side effects. For maximum properties a post cure may be required – Contact our technical service department for advice.

Processing

Mix ratio by weight 9.32:1
Mix ratio by volume 10.57:1

Approvals

RoHS compliant	Yes
UL94-V0	NO
REACH (SVHC concentration)	0%

Typical Properties

Test	Result	Unit
Hardness	78	Shore A
Operating Temperature	-60 - +130	°C (application & geometry dependent)
Abrasion resistance	110	mm ³
Tensile Strength	21	MPa
Elongation at break	600	%
Tear resistance	50	MPa
Water resistance (24hrs @ 23°C)	0.12	%
Water resistance (7 days @ 23°C)	0.78	%

Packaging & Part Numbers

EL217C is available in Bulk, Twinpacks & Kits

Availability

Available through distribution and sales@robnor.co.uk

Cartridge Mixing

Not Available	
---------------	--

It is essential for best results that the cartridge is 'balanced' before use to ensure correct mixing. Loading the cartridge into the gun before attaching the mixer element and pumping the gun to push a small amount of the contents forward will achieve this. Wipe the excess from the cartridge tip and add the static mixer. The cartridge is now ready for use.

Twinpacks

EL217C/BK/100	EL217C/BK/500
EL217C/BK/250	EL217C/BK/1000

Twinpacks are pre-weighed resin and hardener components contained in a tough flexible film, separated by a removable clip and rail. Once the clip and rail is removed the resin and hardener is thoroughly mixed within the bag and is immediately ready for use. Mixing will normally take ~ 2 minutes due to the viscosity; but pay special attention to the corners. Twinpacks are ideal for small to medium production runs, prototyping and on-site or field use. The twinpack weight/volume may also be tailored to a specific size on request.

For further details please visit www.robnor.co.uk

Bulk Materials

RL217C/BK/5KG	HL217C/NC/20KG
RL217C/BK/20KG	

Both resin and hardener are supplied in 5kg, 25kg and 200ltr drums and fully evacuated and ready for use. Care should be taken to ensure when mixing the resins air is not entrained in the mixture. If this is unavoidable the mixed resin and hardener should be re-evacuated before dispensing. The bulk resin and hardener materials can be dispensed from suitable dispensing machinery and Robnor Resins produce a range of these machines, details that can be provided on request.

Kits & Sets

EL217C/BK/1KGKIT	
EL217C/BK/5KGKIT	

Kits and Sets are provided in separate containers to the correct ratio. In Kit form, pour the hardener into the larger resin container and use it as a mixing vessel. Stir well using an appropriate mixer until homogeneous.

Note: Incomplete mixing will be characterised by erratic or partially incomplete cure even after extended time periods.

Cleaning

All equipment contaminated with mixed material should be cleaned before the material has hardened. TS130 is a suitable non-flammable cleaning agent, although other solvents may be found suitable. TS130 will also remove cured material provided it is allowed to soak for a number of hours.

Storage and Shelf Life

Material stored in the original unopened containers under cool dry condition between 15° and 25°C will have a shelf life of at least two years. Once used the containers must be kept sealed to prevent effects from water, air or contaminants.

Health and Safety

Polyurethane resin systems may cause sensitisation by skin contact or inhalation may be corrosive, harmful or toxic. It is therefore strongly recommended that skin and eye contact is avoided by the using of appropriate personal protective equipment such as gloves, safety glasses or goggles and overalls. Wash any contamination from the skin immediately and thoroughly and do not eat, smoke or drink in the working vicinity.

Under normal working conditions a good source of ventilation is adequate, however if the material is heated, or where vapour levels are likely to exceed the occupational exposure limits appropriate respiratory protection must be worn. Local exhaust ventilation (LEV) may be required especially for curing ovens or where large volumes of material are curing. The above is given as a guide only; please refer to RL/HL217C Health and Safety data or our Technical Service Department for individual/specific advice.

Copyright & Warranty - Robnor Resins Limited

The results and information above does not constitute a specification and is given in good faith and without warranty. The information is derived from test/or extrapolations believed to be reliable and is quoted for guidance only. The product is offered for evaluation on the understanding the customer satisfies himself that the product is suitable for his intended by proper evaluation and testing.

Contact Details

Robnor Resins Limited
Hunts Rise
South Marston Park
Swindon SN3 4TE
United Kingdom

Tel: +44 (0) 1793 823741

Fax: +44 (0) 1793 827033

Email: support@robnor.co.uk

Web: www.robnor.co.uk

Buy Online: www.resins-online.com (UK only)