



For more Information
please call

1-800-Belden1



General Description:

20 and 22 AWG stranded tinned copper conductors, foam HDPE (22 AWG) and PVC (20 AWG) insulation, twisted pairs, tinned copper braid shield (95% coverage) drain wire, PVC jacket.

Usage (Overall)

Suitable Applications: IEEE 802.3 Transceiver Cable

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (mm)
3	22	7x30	TC - Tinned Copper	0.762
1	20	7x28	TC - Tinned Copper	0.9652

Total Number of Conductors: 8

Insulation

Insulation Material:

Insulation Trade Name	Insulation Material	Wall Thickness (mm)	AWG
Datalene®	FHDPE - Foam High Density Polyethylene	0.432	22
	PVC - Polyvinyl Chloride	0.305	20

Inner Shield

Inner Shield Material:

Layer #	Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
1	Beldfoil® (Z-Fold®)	Tape (each pair)	Aluminum Foil-Polyester Tape	100.000

Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Braid	TC - Tinned Copper	95

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
22	7x30	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.813

Overall Cable

Overall Nominal Diameter: 8.026 mm

Pair

Pair Color Code Chart:

Number	Color
78 Ohm	Black & White
78 Ohm	Yellow & Orange
78 Ohm	Blue & Green
Power Pair	Gray & Purple

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +80°C
UL Temperature Rating:	80°C (UL AWM Style 2919)
Bulk Cable Weight:	96.733 Kg/Km
Max. Recommended Pulling Tension:	711.712 N
Min. Bend Radius/Minor Axis:	82.550 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CM
NEC Articles:	800
CEC/C(UL) Specification:	CM
AWM Specification:	UL Style 2919 (30 V 80°C)
IEEE Specification:	IEEE802.3
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1685 UL Loading
CSA Flame Test:	FT1

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Description	Impedance (Ohm)	Tolerance (Ohms)
22AWG pairs	78.000	± 5

Nom. Capacitance Conductor to Conductor:

Description	Capacitance (pF/m)
22AWG pairs	54.793

Nom. Capacitance Cond. to Other Conductor & Shield:

Description	Capacitance (pF/m)
22AWG pairs	96.790

Nominal Velocity of Propagation:

Description	VP (%)
22AWG pairs	78.000

Nominal Delay:

Description	Delay (ns/m)
22AWG pairs	4.265

METRIC MEASUREMENT VERSION

9891 Multi-Conductor - 10 Base 5 Transceiver

Nom. Conductor DC Resistance:

Description	DCR @ 20°C (Ohm/km)
22 AWG	48.2307
20 AWG	31.1695

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
5.9058

Max. Operating Voltage - UL:

Voltage	Description
300 V RMS	UL type CM
30 V RMS	UL AWM Style 2919

Max. Recommended Current:

Description	Current
22 awg (10C Temperature Rise)	2 amps per conductor @ 25C ambient
20 awg (10C Temperature Rise)	2.5 amps per conductor @ 25C ambient

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9891 006100	30 MT	3.311 KG	BLUE, LIGHT		4PR1#20,3#22 SH PVC
9891 0061000	305 MT	31.298 KG	BLUE, LIGHT	C	4PR1#20,3#22 SH PVC
9891 006500	152 MT	16.103 KG	BLUE, LIGHT	C	4PR1#20,3#22 SH PVC
9891 0065000	1,524 MT	163.294 KG	BLUE, LIGHT	C Z	4PR1#20,3#22 SH PVC

Notes:

C = CRATE REEL PUT-UP.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND (+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 3 Revision Date: 08-06-2013

© 2013 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.