

# SAFETY DATA SHEET RED SCC3 CONFORMAL COATING

## SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier	
Product name	RED SCC3 CONFORMAL COATING
Product No.	DCR, EDCR01L, EDCR05L, ZE
1.2. Relevant identified uses of th	e substance or mixture and uses advised against
Identified uses	Conformal coating for appliance protection
Uses advised against	At this moment in time we do not have information on use restrictions. They will be included in this safety data sheet when available
1.3. Details of the supplier of the	safety data sheet
Supplier	ELECTROLUBE. A division of HK
	WENTWORTH LTD
	ASHBY PARK, COALFIELD WAY,
	ASHBY DE LA ZOUCH, LEICESTERSHIRE
	LE65 1JR
	UNITED KINGDOM
	+44 (0)1530 419600
	+44 (0)1530 416640
	info@hkw.co.uk

## 1.4. Emergency telephone number

+44 (0)1530 419600 between 8.30am - 5.00pm GMT Mon - Fri

## SECTION 2: HAZARDS IDENTIFICATION

### 2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Classification (1999/45/EEC)

Physical and Chemical<br/>HazardsFlam. Liq. 3 - H226Human healthAcute Tox. 4 - H312;Acute Tox. 4 - H332;Skin Irrit. 2 - H315EnvironmentNot classified.Xn;R20/21. Xi;R38. R10.Value Tox. 4 - H312;Acute Tox. 4 - H332;Skin Irrit. 2 - H315

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

## 2.2. Label elements

Contains XYLENE Label In Accordance With (EC) No. 1272/2008



Signal Word Hazard Statements Warning

H226	Flammable liquid and vapour.
H312	Harmful in contact with skin.
H315	Causes skin irritation.
H332	Harmful if inhaled.

Precautionary Statements		
	P271	Use only outdoors or in a well-ventilated area.
	P280	Wear protective gloves, eye and face protection.
Supplementary Precautionary Stater	ments	
	P210	Keep away from heat/sparks/open flames/hot surfaces No smoking.
	P261	Avoid breathing vapour/spray.
	P302+352	IF ON SKIN: Wash with plenty of soap and water.
Supplemental label information		
	EUH208	Contains ETHYL METHYL KETOXIME. May produce an allergic reaction.

## 2.3. Other hazards

Not Classified as PBT/vPvB by current EU criteria.

## SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

### 3.2. Mixtures

XYLENE			30-60%
CAS-No.: 1330-20-7	EC No.: 215-535-7		
Classification (EC 1272/2008) Flam. Liq. 3 - H226 Acute Tox. 4 - H312 Acute Tox. 4 - H332 Skin Irrit. 2 - H315		Classification (67/548/EEC) R10 Xn;R20/21 Xi;R38	
ETHYLBENZENE			5-10%
CAS-No.: 100-41-4	EC No.: 202-849-4		
Classification (EC 1272/2008) Flam. Liq. 2 - H225 Acute Tox. 4 - H332		Classification (67/548/EEC) F;R11 Xn;R20	
BENZENE, C10-13-ALKYL DERIV	ATIVES		<0.5%
CAS-No.: 67774-74-7	EC No.: 267-051-0		
Classification (EC 1272/2008) Not classified.		Classification (67/548/EEC) N;R50.	
ETHYL METHYL KETOXIME			<0.5%
CAS-No.: 96-29-7	EC No.: 202-496-6		
Classification (EC 1272/2008) Acute Tox. 4 - H312 Eye Dam. 1 - H318 Skin Sens. 1 - H317 Carc. 2 - H351		Classification (67/548/EEC) Carc. Cat. 3;R40 Xn;R21 R43 Xi;R41	

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

### **Composition Comments**

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels.

## SECTION 4: FIRST AID MEASURES

### 4.1. Description of first aid measures

### Inhalation

Move the exposed person to fresh air at once. Keep the affected person warm and at rest. Get prompt medical attention. **Ingestion** 

DO NOT INDUCE VOMITING! Rinse mouth thoroughly. Get medical attention immediately!

### Skin contact

Wash the skin immediately with soap and water. Get medical attention if irritation persists after washing.

### Eye contact

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Contact physician if irritation persists. Use tepid water for rinsing

### 4.2. Most important symptoms and effects, both acute and delayed

## 4.3. Indication of any immediate medical attention and special treatment needed

Treat Symptomatically.

## SECTION 5: FIREFIGHTING MEASURES

## 5.1. Extinguishing media

### Extinguishing media

Fire can be extinguished using: Foam. Dry chemicals, sand, dolomite etc.

### 5.2. Special hazards arising from the substance or mixture

### Hazardous combustion products

Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.

## **Unusual Fire & Explosion Hazards**

Aerosol cans may explode in a fire. May explode when heated or when exposed to flames or sparks. Vapours are heavier than air and may spread near ground to sources of ignition.

### Specific hazards

Aerosol containers can explode when heated, due to excessive pressure build-up.

### 5.3. Advice for firefighters

### **Special Fire Fighting Procedures**

Avoid breathing fire vapours. Cool containers exposed to flames with water until well after the fire is out. **Protective equipment for fire-fighters** 

Self contained breathing apparatus and full protective clothing must be worn in case of fire.

## SECTION 6: ACCIDENTAL RELEASE MEASURES

## 6.1. Personal precautions, protective equipment and emergency procedures

Wear protective clothing as described in Section 8 of this safety data sheet.

### 6.2. Environmental precautions

Do not discharge into drains, water courses or onto the ground.

### 6.3. Methods and material for containment and cleaning up

Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Clean-up personnel should use respiratory and/or liquid contact protection. Absorb in vermiculite, dry sand or earth and place into containers.

## 6.4. Reference to other sections

Wear protective clothing as described in Section 8 of this safety data sheet. See section 11 for additional information on health hazards. For waste disposal, see section 13.

## SECTION 7: HANDLING AND STORAGE

## 7.1. Precautions for safe handling

Avoid spilling, skin and eye contact. Keep away from heat, sparks and open flame. Ventilate well, avoid breathing vapours. Use approved respirator if air contamination is above accepted level.

## 7.2. Conditions for safe storage, including any incompatibilities

Flammable/combustible - Keep away from oxidisers, heat and flames. Store in tightly closed original container in a dry, cool and well-ventilated place. Keep in original container.

## Storage Class

Flammable compressed gas storage.

## 7.3. Specific end use(s)

The identified uses for this product are detailed in Section 1.2.

## SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

## 8.1. Control parameters

Name	STD	TWA	- 8 Hrs	STEL	- 15 Min	Notes
ETHYLBENZENE	WEL	100	441	125	552	
		ppm(Sk)	mg/m3(Sk)	ppm(Sk)	mg/m3(Sk)	
XYLENE	WEL	50 ppm	220 mg/m3	100 ppm	441 mg/m3	Sk

WEL = Workplace Exposure Limit.

Sk = Can be absorbed through skin.

## 8.2. Exposure controls

### Protective equipment



### Process conditions

Use engineering controls to reduce air contamination to permissible exposure level.

### **Engineering measures**

Provide adequate ventilation, including appropriate local extraction, to ensure that the defined occupational exposure limit is not exceeded.

### **Respiratory equipment**

Respiratory protection must be used if air contamination exceeds acceptable level. In case of inadequate ventilation and work of brief duration, use suitable respiratory equipment. Use respiratory equipment with combination filter, type A2/P3. EN14387

## Hand protection

Use suitable protective gloves if risk of skin contact. The most suitable glove must be chosen in consultation with the gloves supplier, who can inform about the breakthrough time of the glove material.

### Eye protection

Wear approved, tight fitting safety glasses where splashing is probable.

### **Other Protection**

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact. Hygiene measures

DO NOT SMOKE IN WORK AREA! Wash hands at the end of each work shift and before eating, smoking and using the toilet. Wash promptly with soap & water if skin becomes contaminated. Use appropriate skin cream to prevent drying of skin. When using do not eat, drink or smoke.

## SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

## 9.1. Information on basic physical and chemical properties

Appearance	Liquid
Colour	Red.
Odour	Aromatic.
Solubility	Immiscible with water
Initial boiling point and boiling range (°C)	137 - 143 (278.6 - 289.4 F)
Relative density	1.080 @ 20 °C (68 F)
Vapour pressure	1 kPa @ 30 °C (86 F)

27 (80.6 F) CC (Closed cup). 1.1 7

## 9.2. Other information

## SECTION 10: STABILITY AND REACTIVITY

## 10.1. Reactivity

There are no known reactivity hazards associated with this product.

## 10.2. Chemical stability

Stable under normal temperature conditions.

## 10.3. Possibility of hazardous reactions

Not available. Hazardous Polymerisation Will not polymerise.

### 10.4. Conditions to avoid

Avoid heat. Avoid contact with oxidisers or reducing agents.

### 10.5. Incompatible materials

Materials To Avoid Strong oxidising substances.

### 10.6. Hazardous decomposition products

Fire creates: Toxic gases/vapours/fumes of: Carbon monoxide (CO). Carbon dioxide (CO2).

## SECTION 11: TOXICOLOGICAL INFORMATION

## 11.1. Information on toxicological effects

### General information

Prolonged and repeated contact with solvents over a long period may lead to permanent health problems.

### Inhalation

Vapours may cause headache, fatigue, dizziness and nausea. Vapour may irritate respiratory system or lungs.

### Ingestion

Harmful if swallowed. Swallowing concentrated chemical may cause severe internal injury. May cause liver and/or renal damage.

### Skin contact

Acts as a defatting agent on skin. May cause cracking of skin, and eczema. Prolonged or repeated exposure may cause severe irritation.

## Eye contact

Irritating to eyes. Vapour or spray may cause temporary (reversible) eye damage.

### Toxicological information on ingredients.

# RED SCC3 CONFORMAL COATING XYLENE (CAS: 1330-20-7)

Acute toxicity:

Acute Toxicity (Oral LD50) 3523 mg/kg Rat

Acute Toxicity (Dermal LD50)

12126 mg/kg Rabbit

## Acute Toxicity (Inhalation LC50)

2700 mg/l (vapours) Rabbit 4 hours

## Aspiration hazard:

Inhalation

Harmful by inhalation. Upper respiratory irritation. Central nervous system depression. Vapours may cause drowsiness and dizziness.

## Ingestion

Swallowing concentrated chemical may cause severe internal injury. May cause nausea, headache, dizziness and intoxication. Diarrhoea.

## Skin contact

Harmful in contact with skin. Irritating to skin.

## Eye contact

May cause severe irritation to eyes.

## Target Organs

Central nervous system Liver Kidneys

# PROPAN-2-OL (CAS: 67-63-0)

## Acute toxicity:

Acute Toxicity (Oral LD50) 5280 mg/kg Rat

# Acute Toxicity (Dermal LD50)

12800 mg/kg Rabbit

## Acute Toxicity (Inhalation LC50)

72.6 mg/l (vapours) Rat 4 hours

## SECTION 12: ECOLOGICAL INFORMATION

## Ecotoxicity

No data on possible environmental effects have been found.

## Ecological information on ingredients.

## XYLENE (CAS: 1330-20-7)

## Ecotoxicity

The product components are not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

## 12.1. Toxicity

## XYLENE (CAS: 1330-20-7)

### Acute Toxicity - Aquatic Invertebrates

EC50 48 hours 1.0 mg/l Daphnia magna Acute Toxicity - Aquatic Plants IC50 72 hours 2.2 mg/l

### PROPAN-2-OL (CAS: 67-63-0)

### Acute Toxicity - Fish

LC50 96 hours 9640 mg/l Pimephales promelas (Fat-head Minnow) Acute Toxicity - Aquatic Invertebrates EC50 48 hours 13299 mg/l Daphnia magna Acute Toxicity - Aquatic Plants EC50 72 hours > 1.000 mg/l Scenedesmus subspicatus Acute Toxicity - Microorganisms EC50 > 1.000 mg/l Activated sludge

### 12.2. Persistence and degradability

### Degradability

There are no data on the degradability of this product.

### Ecological information on ingredients.

XYLENE (CAS: 1330-20-7)

### Degradability

The product is biodegradable.

### 12.3. Bioaccumulative potential

### **Bioaccumulative potential**

No data available on bioaccumulation.

Ecological information on ingredients.

## XYLENE (CAS: 1330-20-7)

Bioaccumulation factor BCF 25.9 Partition coefficient 3.2

## 12.4. Mobility in soil

## Ecological information on ingredients.

### Mobility:

XYLENE (CAS: 1330-20-7)

The product is insoluble in water.

## 12.5. Results of PBT and vPvB assessment

This product does not contain any PBT or vPvB substances.

## Ecological information on ingredients.

## XYLENE (CAS: 1330-20-7)

Not Classified as PBT/vPvB by current EU criteria.

### 12.6. Other adverse effects

## Ecological information on ingredients.

XYLENE (CAS: 1330-20-7)

Not determined.

## SECTION 13: DISPOSAL CONSIDERATIONS

## 13.1. Waste treatment methods

Dispose of waste and residues in accordance with local authority requirements.

SECTION '	4: TRANSPORT INFORMATION
<u>14.1. UN numb</u>	<u>ər</u>

1263
1263
1263
PAINT
3
Class 3: Flammable liquids.
3
3
3



### 14.4. Packing group

ADR/RID/ADN Packing group	III
IMDG Packing group	III
ICAO Packing group	III

## 14.5. Environmental hazards

Environmentally Hazardous Substance/Marine Pollutant No.

### 14.6. Special precautions for user

EMS	F-E, S-E
Emergency Action Code	•3Y
Hazard No. (ADR)	30
Tunnel Restriction Code	(D/E)

## 14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

No information required.

# SECTION 15: REGULATORY INFORMATION

## 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

### Statutory Instruments

The Chemicals (Hazard Information and Packaging for Supply) Regulations 2009 (S.I 2009 No. 716). Control of Substances Hazardous to Health.

### **Guidance Notes**

Workplace Exposure Limits EH40. **EU Legislation** 

Commission Directive 2000/39/EC of 8 June 2000 establishing a first list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work.

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006 with amendments.

Authorisations (Title VII Regulation 1907/2006)

No specific authorisations are noted for this product.

Restrictions (Title VIII Regulation 1907/2006)

No specific restrictions of use are noted for this product.

## 15.2. Chemical Safety Assessment

No chemical safety assessment has been carried out.

OTHER INFORMATION	SECTION 16: OTHE
Helen O'Reilly	ssued By
APRIL 2013	Revision Date
7	Revision
11413	SDS No.
	Risk Phrases In Full
Flammable.	R10
Harmful by inhalation and in contact with skin.	R20/21
Harmful by inhalation.	R20
Harmful in contact with skin.	R21
Highly flammable	R11
Irritating to skin.	R38
Limited evidence of a carcinogenic effect.	R40
May cause sensitisation by skin contact.	R43
Risk of serious damage to eyes.	R41
Very toxic to aquatic organisms.	R50
ı Full	Hazard Statements In Full
Causes serious eye damage.	H318
Causes skin irritation.	H315
Flammable liquid and vapour.	H226
Harmful if inhaled.	H332
Harmful in contact with skin.	H312
Highly flammable liquid and vapour.	H225
May cause an allergic skin reaction.	H317
Suspected of causing cancer.	H351
Risk of serious damage to eyes. Very toxic to aquatic organisms. Full Causes serious eye damage. Causes skin irritation. Flammable liquid and vapour. Harmful if inhaled. Harmful if inhaled. Harmful in contact with skin. Highly flammable liquid and vapour. May cause an allergic skin reaction.	R41 R50 Hazard Statements In Full H318 H315 H226 H332 H312 H225 H317

### Disclaimer

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.