

97 78 180

Crimping Pliers for end sleeves (ferrules)



- for crimping end sleeves (ferrules) according DIN 46228 parts 1 + 4 from 0.25 to 16 mm²
- improved leverage for 30% easier crimping
- light and slim design
- crimping in marked half-round dies for reliable connections between the sleeve and the conductor
- 9 particularly deep dies with conical side faces
- Special tool steel, forged, oil-hardened



Article No.	97 78 180
EAN	4003773072003
Head	polished
Handles	insulated with multi-component grips, VDE-tested
Insulation standard	IEC 60900 DIN EN 60900
Applications	End Sleeves (ferrules)
Capacity mm²	0,25 - 16,0
Number of crimping positions	9
AWG	23 - 5
Length mm	180
Net weight g	254



technical change and errors excepted