

SACC-FS-17PCON SCO

Order No.: 1559644

<http://eshop.phoenixcontact.co.uk/phoenix/treeViewClick.do?UID=1559644>

Sensor/actuator connector, female connector, straight, 17-pos., M12 SPEEDCON, metal knurl, Piercecon[®], maximum cable diameter of 8.2 mm



Commercial data

EAN	 4 046356 314862
Pack	1
Customs tariff	85366990
Gross weight in pieces	35.50 g
Country of Origin	DE
Catalog page information	Page 19 (C-4-2013)

Product notes

WEEE/RoHS-compliant since:
07/09/2007



Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation at <http://www.download.phoenixcontact.com>. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

Dimensions

Wrench size, union nut	13 mm
External diameter	5.4 mm ... 8.2 mm
Stripping length of the sheath	≥ 60 mm

Ambient conditions

Ambient temperature (operation)	-25 °C ... 85 °C (Plug / socket)
Degree of protection	IP67

General

Rated current at 40°C	1.5 A
Rated voltage	30 V
Number of positions	17
Contact resistance	≤ 5 mΩ
Insulation resistance	≥ 100 MΩ
Coding	A - standard
Standards/regulations	M12 connector IEC 61076-2-101
Status display	No
Surge voltage category	II
Pollution degree	3
Connection method	Piercecon® fast connection
Conductor cross section	0.14 mm ²
AWG conductor cross section	26
Wire diameter including insulation	0.95 mm ... 1.05 mm
Frequency of connections between conductors of the same cross section	≥ 5
Wire insulation material	PUR/PVC
Structure of individual litz in acc. with VDE 0295 / smallest wire diameter	VDE 0295 Class 6
Insertion/withdrawal cycles	≥ 100
Torque	0.4 Nm (M12 knurl)

Material

Inflammability class according to UL 94	V0
Contact material	CuZn
Contact surface material	Ni/Au
Contact carrier material	PA
Material of grip body	Zinc die-cast, nickel-plated
Material, knurls	Zinc die-cast, nickel-plated
Sealing material	FKM

Certificates



Certification GOST

Certifications applied for:


Certification Ex:

Accessories

Item	Designation	Description
Cable/conductor		
1441545	SAC-17P-100,0-PVC/0,14	Sensor/Actuator cable, 17-position, PVC, Black RAL 9005, Free cable end, on Free cable end, Cable length: 100 m
Protection and sealing elements		
1430899	PROT-M12 MS-PA-CHAIN	M12 sealing cap with fixing band, for sensor cables, for free M12 sockets
Tools		
1212487	MICROFOX-SP-1	Electronic diagonal cutter, tapered head, without chamfer, with opening spring, non-reflective phosphate-treated surface, punched version
1208432	SAC BIT M12-D15	Nut for assembling sensor/actuator cables with M12 connector and for M12 connectors with QUICKON fast connection technology, for 4 mm hexagonal drive
1208429	TSD 04 SAC	Torque screwdriver, with preset torque of 0.4 Nm and 4 mm hexagonal drive for M12 connectors
1212224	TSD-M 1,2NM	Torque screw driver, accuracy as per EN ISO 6789 standard, adjustable from 0.3 - 1.2 Nm
1212600	TSD-M SAC-BIT ADAPTER	Adapter bit for TSD-M...torque tools, E6.3-1/4" drive with 4 mm hexagon to accommodate SAC bits


Drawings

Dimensioned drawing



M12 x 1 socket, straight

Schematic diagram



Pin assignment M12, 17-pos., socket side view

Address

PHOENIX CONTACT Ltd
Halesfield 13
Telford / Shropshire / TF7 4PG,England
Phone 01952 681 700
Fax 01952 681 799
<http://www.phoenixcontact.co.uk>



Phoenix Contact Ltd.
Technical modifications reserved;