



Revision Number: 003.0

Issue date: 05/08/2012

1. PRODUCT AND COMPANY IDENTIFICATION

Product name: LOCTITE 243 THREADLOCKER 50ML	IDH number: 1329467
Product type: Anaerobic	Item number: 1329467
	Region: United States
Company address: Henkel Corporation One Henkel Way Rocky Hill, Connecticut 06067	Contact information: Telephone: 860.571.5100 MEDICAL EMERGENCY Phone: Poison Control Center 1-877-671-4608 (toll free) or 1-303-592-1711 TRANSPORT EMERGENCY Phone: CHEMTREC 1-800-424-9300 (toll free) or 1-703-527-3887 Internet: www.henkelna.com

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

Physical state: Liquid	HEALTH: *2
Color: Blue	FLAMMABILITY: 1
Odor: Characteristic	PHYSICAL HAZARD: 1
	Personal Protection: See MSDS Section 8

HMIS:

WARNING: CAUSES EYE IRRITATION.
MAY CAUSE ALLERGIC SKIN REACTION.
MAY CAUSE SKIN AND RESPIRATORY TRACT IRRITATION.

Relevant routes of exposure: Skin, Inhalation, Eyes

Potential Health Effects

Inhalation:	May cause respiratory tract irritation.
Skin contact:	May cause allergic skin reaction. May cause skin irritation with discomfort or rash.
Eye contact:	Contact with eyes will cause irritation. Pain and discomfort. Excess tearing.
Ingestion:	May be harmful if swallowed.

Existing conditions aggravated by exposure: Eye, skin, and respiratory disorders.

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous components	CAS NUMBER	%
Polyglycol dimethacrylate	25852-47-5	10 - 30
Tetramethylene dimethacrylate	2082-81-7	10 - 30
Adipic acid polymer with neopentylglycol, 1,4-butanediol and isononanol	208945-12-4	10 - 30
2,4,6-Triallyloxy-1,3,5-triazine	101-37-1	5 - 10
2-[[2,2-bis[[[(1-oxoallyl)oxy]methyl]butoxy]methyl]-2-ethyl-1,3-propanediyl diacrylate	94108-97-1	1 - 5
Amorphous fumed silica	68611-44-9	1 - 5
Propanediol-1,2	57-55-6	1 - 5
Polyamide resin	Proprietary	1 - 5
1-Acetyl-2-phenylhydrazine	114-83-0	0.1 - 1
Cumene	98-82-8	0.1 - 1

4. FIRST AID MEASURES

Inhalation:	Move to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. If symptoms develop and persist, get medical attention.
Skin contact:	Wash with soap and water. Remove contaminated clothing and footwear. Wash clothing before reuse. If symptoms develop and persist, get medical attention.
Eye contact:	Flush with copious amounts of water, preferably, lukewarm water for at least 15 minutes, holding eyelids open all the time. Get medical attention.
Ingestion:	Do not induce vomiting. Keep individual calm. Get medical attention.

5. FIRE FIGHTING MEASURES

Flash point:	> 93 °C (> 199.4 °F)
Autoignition temperature:	Not available.
Flammable/Explosive limits - lower:	Not available.
Flammable/Explosive limits - upper:	Not available.
Extinguishing media:	Foam, dry chemical or carbon dioxide.
Special firefighting procedures:	Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.
Unusual fire or explosion hazards:	None
Hazardous combustion products:	Oxides of carbon. Oxides of sulfur. Oxides of nitrogen. Irritating organic fragments.

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions:	Do not allow product to enter sewer or waterways.
Clean-up methods:	Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Store in a partly filled, closed container until disposal.

7. HANDLING AND STORAGE

Handling:	Avoid contact with eyes, skin and clothing. Avoid breathing vapors or mists of this product. Wash thoroughly after handling.
Storage:	For safe storage, store at or below 38 °C (100.4 °F) Keep in a cool, well ventilated area away from heat, sparks and open flame. Keep container tightly closed until ready for use.

For information on product shelf life contact Henkel Customer Service at (800) 243-4874.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous components	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Polyglycol dimethacrylate	None	None	None	None
Tetramethylene dimethacrylate	None	None	None	None
Adipic acid polymer with neopentylglycol, 1,4-butanediol and isononanol	None	None	None	None
2,4,6-Triallyloxy-1,3,5-triazine	None	None	None	None
2-[[[2,2-bis[[[(1-oxoallyl)oxy]methyl]butoxy]methyl]-2-ethyl-1,3-propanediyl diacrylate	None	None	None	None
Amorphous fumed silica	None	None	None	None
Propanediol-1,2	None	None	10 mg/m3 TWA Aerosol.	None
Polyamide resin	None	None	None	None
1-Acetyl-2-phenylhydrazine	None	None	None	None
Cumene	50 ppm TWA	50 ppm (245 mg/m3) TWA (SKIN)	None	None

Engineering controls:

Local exhaust ventilation is recommended when general ventilation is not sufficient to control airborne contamination.

Respiratory protection:

Use a NIOSH approved air-purifying respirator with an organic vapor cartridge.

Eye/face protection:

Safety goggles or safety glasses with side shields.

Skin protection:

Use impermeable gloves and protective clothing as necessary to prevent skin contact. Neoprene, Butyl-rubber, or nitrile-rubber gloves.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state:	Liquid
Color:	Blue
Odor:	Characteristic
Odor threshold:	Not available.
pH:	Not available.
Vapor pressure:	< 0.1 mm hg (27 °C (80.6 °F))
Boiling point/range:	> 149 °C (> 300.2 °F)
Melting point/ range:	Not available.
Specific gravity:	1.09
Vapor density:	Not available.
Flash point:	> 93 °C (> 199.4 °F)
Flammable/Explosive limits - lower:	Not available.
Flammable/Explosive limits - upper:	Not available.
Autoignition temperature:	Not available.
Evaporation rate:	Not available.
Solubility in water:	Slight
Partition coefficient (n-octanol/water):	Not available.
VOC content:	4.25 %; 46.4 g/l

10. STABILITY AND REACTIVITY

Stability:	Stable
Hazardous reactions:	Will not occur.
Hazardous decomposition products:	Oxides of carbon. Oxides of nitrogen. Oxides of sulfur. Irritating organic fragments.
Incompatible materials:	Strong oxidizing agents. Reducing agents. Strong alkalis. Oxygen scavengers. Other polymerization initiators. Heavy metals.
Conditions to avoid:	See "Handling and Storage" (Section 7) and "Incompatibility" (Section 10).

11. TOXICOLOGICAL INFORMATION

Hazardous components	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Polyglycol dimethacrylate	No	No	No
Tetramethylene dimethacrylate	No	No	No
Adipic acid polymer with neopentylglycol, 1,4-butanediol and isononanol	No	No	No
2,4,6-Triallyloxy-1,3,5-triazine	No	No	No
2-[[2,2-bis[[[1-oxoallyl]oxy]methyl]butoxy]methyl]-2-ethyl-1,3-propanediyl diacrylate	No	No	No
Amorphous fumed silica	No	No	No
Propanediol-1,2	No	No	No
Polyamide resin	No	No	No
1-Acetyl-2-phenylhydrazine	No	No	No
Cumene	No	Group 2B	No

Hazardous components	Health Effects/Target Organs
Polyglycol dimethacrylate	Irritant, Allergen
Tetramethylene dimethacrylate	Irritant, Allergen
Adipic acid polymer with neopentylglycol, 1,4-butanediol and isononanol	No Data
2,4,6-Triallyloxy-1,3,5-triazine	No Target Organs
2-[[2,2-bis[[[1-oxoallyl]oxy]methyl]butoxy]methyl]-2-ethyl-1,3-propanediyl diacrylate	No Data
Amorphous fumed silica	No Target Organs
Propanediol-1,2	Irritant
Polyamide resin	No Records
1-Acetyl-2-phenylhydrazine	Allergen, Blood, Kidney, Mutagen, Some evidence of carcinogenicity
Cumene	Central nervous system, Irritant, Lung

12. ECOLOGICAL INFORMATION

Ecological information: Not available.

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Follow all local, state, federal and provincial regulations for disposal.

Hazardous waste number: Not a RCRA hazardous waste.

14. TRANSPORT INFORMATION

The shipping classifications in this sections are for non-bulk packaging only (unless otherwise specified). Shipping classification may be different for bulk packaging.

U.S. Department of Transportation Ground (49 CFR)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

International Air Transportation (ICAO/IATA)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

Water Transportation (IMO/MDG)

Proper shipping name:	Not regulated
Hazard class or division:	None
Identification number:	None
Packing group:	None

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status:	All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.
TSCA 12(b) Export Notification:	None above reporting de minimus
CERCLA/SARA Section 302 EHS:	None above reporting de minimus
CERCLA/SARA Section 311/312:	Immediate Health, Delayed Health
CERCLA/SARA 313:	None above reporting de minimus
California Proposition 65:	This product contains a chemical known in the State of California to cause cancer. This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

Canada Regulatory Information

CEPA DSL/NDL Status:	All components are listed on or are exempt from listing on the Canadian Domestic Substances List.
WHMIS hazard class:	D.2.B

16. OTHER INFORMATION

This material safety data sheet contains changes from the previous version in sections: 3, 8, 11, 15

Prepared by: Kyra Kozak Woods, Manager, Regulatory Affairs

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.