



The Model HL1910E is a variable temperature electronic heat gun. This heat gun performs with maximum reliability and flexible use. Some recommended applications: plastic welding, packaging, automotive, maintenance, or any application requiring precise reduction of heat output.

Featuring Steinel's patented DuraTherm™ heating system, this heat gun distributes heat evenly through its coils. The coils are wound through a stack of ceramic disks for a "honey-comb" type effect. The ceramic disks prevent any hot or cold spots from forming, and provide the most evenly heated airflow available. The exclusive DuraTherm™ heating element and adjustable temperature wheel makes it possible to complete a wide variety of applications with this heat gun.



Model HL1910E

Model HL1910E Specifications:

Housing Material	PBT (Polybutylene Terephthalate)	Switch	Fully enclosed slide switch
Self Extinguishing Material	Yes	Switch Functional Positions	High, Low, Cold, and Off
Current Type	AC	Power Cord	Industrial grade rubber
Voltage	120 Volts	Overall Length	9-1/2"
Frequency	60 Hz	Overall Width	3-1/4"
Phase	Single	Overall Height	8"
Double Insulated	Yes	Weight	30 ounces
Wattage Rating	1500 watts	Fungus Resistant	Yes
Heating Element	Ceramic encapsulated	Suspension Feature	Available hanger, built in stand
Temp Rating	120° F (min) and 1100° F (max)	Special Features	ROHS/WEEE/PENTADBE/OCTADBE Compliant
Temperature Control	Electronic thermocouple	Ability to use Reduction Nozzles	Yes
Air Flow	High and low setting independent of temperature	Certifications	UL, CUL (complies with UL standard 499)
Air Pressure	1000 PA	Origin	European Union

Distributed by: ALL-SPEC INDUSTRIES
 WILMINGTON, NC 28401
www.all-spec.com

Phone: 800-537-0351
Fax: 800-379-9903
Email: sales@all-spec.com