



For more Information  
please call

1-800-Belden1



## General Description:

EPDM is naturally corona and more heat resistant than many other rubber compounds and is able to take longer bake cycles frequently needed for big jobs. EPDM has superior weather resistance and low temperature pliability.

## Physical Characteristics (Overall)

### Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
1	1	210x24	TC - Tinned Copper

Total Number of Conductors: 1

### Insulation

Insulation Material:

Insulation Material	Min. Avg. Wall (mm)
EPDM - Ethylene Propylene Diene Monomer Rubber	3.175

### Separator

Separator Material over Conductor: Y

### Overall Insulation

#### Overall Cable

Overall Nominal Diameter: 16.205 mm

## Mechanical Characteristics (Overall)

Operating Temperature Range: -55°C To +150°C

Bulk Cable Weight: 587.839 Kg/Km

## Applicable Specifications and Agency Compliance (Overall)

### Applicable Standards & Environmental Programs

UL Rating: 7500 V, 150°C

EU Directive 2011/65/EU (ROHS II): Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

### Plenum/Non-Plenum

Plenum (Y/N): No

## Electrical Characteristics (Overall)

Nom. Conductor DC Resistance:

METRIC MEASUREMENT VERSION

37501 Hook-up/Lead - UL AWM Style 3499

**DCR @ 20°C (Ohm/km)**

0.394

**Max. Operating Voltage - UL:**

Voltage	Description
7500 VRMS	UL AWM 3499

**Max. Recommended Current:**

Description	Current
Single conductor in free air @ 30C ambient	293 amps

**Put Ups and Colors:**

Item #	Putup	Ship Weight	Color	Notes	Item Desc
37501 01050	15 MT	10.455 KG	BLACK	C	#1 EPDM 150C 7.5KV AC
37501 010500	152 MT	97.296 KG	BLACK	C F	#1 EPDM 150C 7.5KV AC

**Notes:**

C = CRATE REEL PUT-UP.

F = MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 50'

Revision Number: 1      Revision Date: 08-30-2013

© 2013 Belden, Inc.  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.