

SAFETY DATA SHEET SCREEN AND STENCIL SOLVENT

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product name SCREEN AND STENCIL SOLVENT
Product No. SSS, ESSS500ML, ESSS05L, ESSS25L, ZE

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Cleaning Product
Uses advised against At this moment in time we do not have information on use restrictions. They will be included in this safety data sheet when available

1.3. Details of the supplier of the safety data sheet

Supplier ELECTROLUBE. A division of HK WENTWORTH LTD
 ASHBY PARK, COALFIELD WAY,
 ASHBY DE LA ZOUCH, LEICESTERSHIRE
 LE65 1JR
 UNITED KINGDOM
 +44 (0)1530 419600
 +44 (0)1530 416640
 info@hkw.co.uk

1.4. Emergency telephone number

+44 (0)1530 419600 between 8.30am - 5.00pm GMT Mon – Fri

SECTION 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Physical and Chemical Hazards	Not classified.
Human health	Eye Irrit. 2 - H319; STOT SE 3 - H336
Environment	Not classified.

Classification (1999/45/EEC)

Xi; R36. R67.

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

2.2. Label elements

Label In Accordance With (EC) No. 1272/2008



Signal Word

Warning

Hazard Statements

H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.

Precautionary Statements

P280	Wear protective gloves, eye and face protection.
P305+351+338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

SCREEN AND STENCIL SOLVENT

P313
P304+340

Get medical advice/attention.
IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.

Supplementary Precautionary Statements

P261

Avoid breathing vapour/spray.

2.3. Other hazards

Not Classified as PBT/vPvB by current EU criteria.

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

3.2. Mixtures

TETRAHYDROFURFURYL ALCOHOL		60-80%
CAS-No.: 97-99-4	EC No.: 202-625-6	
Classification (EC 1272/2008) Eye Irrit. 2 - H319	Classification (67/548/EEC) Xi;R36	
1-METHOXY-2-PROPANOL		10-30%
CAS-No.: 107-98-2	EC No.: 203-539-1	
Classification (EC 1272/2008) Flam. Liq. 3 - H226 STOT SE 3 - H336	Classification (67/548/EEC) R10 R67	

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

Composition Comments

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels.

SECTION 4: FIRST AID MEASURES

4.1. Description of first aid measures

Inhalation

Move the exposed person to fresh air at once. Perform artificial respiration if breathing has stopped. Keep the affected person warm and at rest. Get prompt medical attention. NOTE! Keep affected person away from heat, sparks and flames!

Ingestion

DO NOT INDUCE VOMITING! NEVER MAKE AN UNCONSCIOUS PERSON VOMIT OR DRINK FLUIDS! Remove victim immediately from source of exposure. Provide fresh air, warmth and rest, preferably in comfortable upright sitting position. Rinse mouth thoroughly. Get medical attention.

Skin contact

Remove affected person from source of contamination. Promptly wash contaminated skin with soap or mild detergent and water. Promptly remove clothing if soaked through and wash as above. Get medical attention if irritation persists after washing.

Eye contact

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

4.2. Most important symptoms and effects, both acute and delayed

4.3. Indication of any immediate medical attention and special treatment needed

Treat Symptomatically.

SECTION 5: FIREFIGHTING MEASURES

5.1. Extinguishing media

Extinguishing media

Use: Alcohol resistant foam. Powder. Dry chemicals, sand, dolomite etc.

SCREEN AND STENCIL SOLVENT

5.2. Special hazards arising from the substance or mixture

Hazardous combustion products

Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.

5.3. Advice for firefighters

Special Fire Fighting Procedures

Ventilate closed spaces before entering them. Move container from fire area if it can be done without risk. Use water to keep fire exposed containers cool and disperse vapours. Do not scatter spilled material with more water than needed to fight the fire. Be aware of danger for fire to re-start. Keep run-off water out of sewers and water sources. Dike for water control.

Protective equipment for fire-fighters

Self contained breathing apparatus and full protective clothing must be worn in case of fire.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Wear protective clothing as described in Section 8 of this safety data sheet.

6.2. Environmental precautions

Do not discharge into drains, water courses or onto the ground.

6.3. Methods and material for containment and cleaning up

Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Stop leak if possible without risk. Wear necessary protective equipment. Absorb in vermiculite, dry sand or earth and place into containers. Small quantities may be flushed to drains with plenty of water.

6.4. Reference to other sections

Wear protective clothing as described in Section 8 of this safety data sheet. See section 11 for additional information on health hazards. Collect and dispose of spillage as indicated in section 13.

SECTION 7: HANDLING AND STORAGE

7.1. Precautions for safe handling

Keep away from heat, sparks and open flame. Avoid spilling, skin and eye contact. Ventilate well, avoid breathing vapours. Use approved respirator if air contamination is above accepted level.

7.2. Conditions for safe storage, including any incompatibilities

Keep in original container. Store in a cool and well-ventilated place.

Storage Class

Miscellaneous hazardous material storage.

7.3. Specific end use(s)

The identified uses for this product are detailed in Section 1.2.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

Name	STD	TWA - 8 Hrs		STEL - 15 Min		Notes
1-METHOXY-2-PROPANOL	WEL	100 ppm	375 mg/m ³	150 ppm	560 mg/m ³	Sk

WEL = Workplace Exposure Limit.

Sk = Can be absorbed through skin.

8.2. Exposure controls

Protective equipment



SCREEN AND STENCIL SOLVENT

Process conditions

Use engineering controls to reduce air contamination to permissible exposure level. Provide eyewash station.

Engineering measures

Provide adequate ventilation, including appropriate local extraction, to ensure that the defined occupational exposure limit is not exceeded.

Respiratory equipment

No specific recommendation made, but respiratory protection must be used if the general level exceeds the recommended occupational exposure limit. In case of inadequate ventilation and work of brief duration, use suitable respiratory equipment. Use respiratory equipment with combination filter, type A2/P3.

Hand protection

Protective gloves must be used if there is a risk of direct contact or splash. The most suitable glove must be chosen in consultation with the gloves supplier, who can inform about the breakthrough time of the glove material.

Eye protection

Wear approved safety goggles.

Other Protection

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

Hygiene measures

DO NOT SMOKE IN WORK AREA! Wash hands at the end of each work shift and before eating, smoking and using the toilet. Wash promptly with soap & water if skin becomes contaminated. Promptly remove any clothing that becomes contaminated. When using do not eat, drink or smoke.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

Appearance	Liquid
Colour	Clear
Initial boiling point and boiling range (°C)	>100 (212 F)
Relative density	1.025 @ 20 °c (68 F)
Flash point (°C)	61 (141.8 F)

9.2. Other information

None.

SECTION 10: STABILITY AND REACTIVITY

10.1. Reactivity

No specific reactivity hazards associated with this product.

10.2. Chemical stability

Stable under normal temperature conditions.

10.3. Possibility of hazardous reactions

Not available.

Hazardous Polymerisation

Will not polymerise.

10.4. Conditions to avoid

Avoid heat, flames and other sources of ignition.

10.5. Incompatible materials

Materials To Avoid

Strong acids. Strong alkalis. Strong oxidising substances.

10.6. Hazardous decomposition products

Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.

SECTION 11: TOXICOLOGICAL INFORMATION

11.1. Information on toxicological effects

SCREEN AND STENCIL SOLVENT

Health Warnings

INHALATION. May cause irritation to the respiratory system. SKIN CONTACT. Prolonged or repeated contact leads to drying of skin. May cause skin irritation/eczema. EYE CONTACT. Irritating to eyes. INGESTION. May cause stomach pain or vomiting.

Toxicological information on ingredients.

TETRAHYDROFURFURYL ALCOHOL (CAS: 97-99-4)

Toxic Dose 1 - LD 50
25000 mg/kg (oral rat)

1-METHOXY-2-PROPANOL (CAS: 107-98-2)

Toxic Dose 1 - LD 50
5200 mg/kg (oral rat)
Toxic Dose 2 - LD 50
11700 mg/kg (oral-mouse)

SECTION 12: ECOLOGICAL INFORMATION

Ecotoxicity

No data on possible environmental effects have been found.

12.1. Toxicity

Ecological information on ingredients.

TETRAHYDROFURFURYL ALCOHOL (CAS: 97-99-4)

EC 50, 48 Hrs, Daphnia, mg/l
8000

1-METHOXY-2-PROPANOL (CAS: 107-98-2)

LC 50, 96 Hrs, Fish mg/l
20800
EC 50, 48 Hrs, Daphnia, mg/l
23300

12.2. Persistence and degradability

Degradability

There are no data on the degradability of this product.

12.3. Bioaccumulative potential

Bioaccumulative potential

No data available on bioaccumulation.

12.4. Mobility in soil

12.5. Results of PBT and vPvB assessment

This product does not contain any PBT or vPvB substances.

12.6. Other adverse effects

The product contains volatile, organic compounds which have a photochemical ozone creation potential.

SECTION 13: DISPOSAL CONSIDERATIONS

General information

Waste is classified as hazardous waste. Disposal to licensed waste disposal site in accordance with the local Waste Disposal Authority.

13.1. Waste treatment methods

Dispose of waste and residues in accordance with local authority requirements.

SECTION 14: TRANSPORT INFORMATION

General

The product is not covered by international regulation on the transport of dangerous goods (IMDG, IATA, ADR/RID).

Road Transport Notes

Not Classified

Rail Transport Notes

Not classified.

SCREEN AND STENCIL SOLVENT

Sea Transport Notes Not classified.

Air Transport Notes Not classified.

14.1. UN number

14.2. UN proper shipping name

14.3. Transport hazard class(es)

Transport Labels

No transport warning sign required.

14.4. Packing group

14.5. Environmental hazards

Environmentally Hazardous Substance/Marine Pollutant

No.

14.6. Special precautions for user

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

No information required.

SECTION 15: REGULATORY INFORMATION

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Statutory Instruments

The Chemicals (Hazard Information and Packaging for Supply) Regulations 2009 (S.I 2009 No. 716). Control of Substances Hazardous to Health.

Guidance Notes

Workplace Exposure Limits EH40.

EU Legislation

Commission Directive 2000/39/EC of 8 June 2000 establishing a first list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work.

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006 with amendments.

Authorisations (Title VII Regulation 1907/2006)

No specific authorisations are noted for this product.

Restrictions (Title VIII Regulation 1907/2006)

No specific restrictions of use are noted for this product.

15.2. Chemical Safety Assessment

No chemical safety assessment has been carried out.

SECTION 16: OTHER INFORMATION

Issued By	Helen O'Reilly
Revision Date	APRIL 2013
Revision	3
SDS No.	10573

SCREEN AND STENCIL SOLVENT

Risk Phrases In Full

R10	Flammable.
R36	Irritating to eyes.
R67	Vapours may cause drowsiness and dizziness.

Hazard Statements In Full

H226	Flammable liquid and vapour.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.

Disclaimer

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.