


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.



SPC Type No.	Wire Size (AWG)	Stud Size	L	W	E	C	T	U	Pkg QTY
CRS-ZO-0425	4	1/4" (.250)	1.34	.68	1.00	.53			10
SPC3753	4	1/4" (.250)	1.34	.68	1.00	.53			100
CRS-ZO-0437	4	3/8" (.375)	1.34	.68	1.00	.53	.280	.075	10
SPC3754	4	3/8" (.375)	1.34	.68	1.00	.53			100
CRS-ZO-0610	6	#10 (.196)	1.14	.47	.91	.52			20
SPC3750	6	#10 (.196)	1.14	.47	.91	.52			200
CRS-ZO-0625	6	1/4" (.250)	1.14	.47	.91	.52	.250		20
SPC3751	6	1/4" (.250)	1.14	.47	.91	.52			200
CRS-ZO-0631	6	5/16" (.312)	1.22	.63	.91	.52			20
SPC3752	6	5/16" (.312)	1.22	.63	.91	.52			200
CRS-ZO-0810	8	#10 (.196)	.95	.47	.72	.40			25
SPC3746	8	#10 (.196)	.95	.47	.72	.40	.050		250
CRS-ZO-0825	8	1/4" (.250)	.95	.47	.72	.40			25
SPC3747	8	1/4" (.250)	.95	.47	.72	.40			250
CRS-ZO-0831	8	5/16" (.312)	1.06	.59	.77	.45	.175		25
SPC3748	8	5/16" (.312)	1.06	.59	.77	.45			250
CRS-ZO-0837	8	3/8" (.375)	1.06	.59	.77	.45			25
SPC3749	8	3/8" (.375)	1.06	.59	.77	.45			250

REVISONS		DOC. NO. SPC-F005	Effective: 12/21/98	DCP No. 680				
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRD	DATE
217	B	Removed Discontinued Part	DJC	6/26/97	JC	7/3/97	JC	7/3/97
1116	C	Add Bulk Items; was CRS-ZO-****	JWM	3/6/01	JC	3/6/01	JC	3/6/01

- NOTES:  
MATERIAL:  
1. ELECTRO-TIN PLATED COPPER  
2. TO BE FREE OF BURRS.  
3. CAN BE CRIMPED ANYWHERE ON BARREL SURFACE.  
4. VOLTAGE RATING AND TEMPERATURE RANGE:  
600 V AND 347°F (175°C)  
5. USE CRIMPING TOOL GROUP A: 8403-001

SPC Type No.	Wire Size (AWG)	Stud Size	L	W	E	C	T	U	Pkg QTY
CRS-ZO-1008	12 ~ 10	#8 (.174)	.68	.28	.54	.29			50
SPC3743	12 ~ 10	#8 (.174)	.68	.28	.54	.29			500
CRS-ZO-1010	12 ~ 10	#10 (.196)	.73	.38	.54	.29	.135	.040	50
SPC3744	12 ~ 10	#10 (.196)	.73	.38	.54	.29			500
CRS-ZO-1025	12 ~ 10	1/4" (.250)	.96	.54	.69	.44			50
SPC3745	12 ~ 10	1/4" (.250)	.96	.54	.69	.44			500
CRS-ZO-1406	16 ~ 14	#6 (.143)	.60	.25	.47	.22			100
SPC3739	16 ~ 14	#6 (.143)	.60	.25	.47	.22			1000
CRS-ZO-1408	16 ~ 14	#8 (.174)	.74	.31	.58	.33			100
SPC3740	16 ~ 14	#8 (.174)	.74	.31	.58	.33	.090		1000
CRS-ZO-1410	16 ~ 14	#10 (.196)	.74	.31	.58	.33			100
SPC3741	16 ~ 14	#10 (.196)	.74	.31	.58	.33	.030		1000
CRS-ZO-1425	16 ~ 14	1/4" (.250)	.89	.47	.65	.40			100
SPC3742	16 ~ 14	1/4" (.250)	.89	.47	.65	.40			1000
CRS-ZO-1806	22 ~ 18	#6 (.143)	.60	.25	.47	.22			100
SPC3737	22 ~ 18	#6 (.143)	.60	.25	.47	.22	.070		1000
CRS-ZO-1808	22 ~ 18	#8 (.174)	.74	.31	.58	.33			100
SPC3738	22 ~ 18	#8 (.174)	.74	.31	.58	.33			1000



ES8918



LR22190M6

OSHA Acceptable

SPC-F005.DWG

DISCLAIMER:  
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE, BY THEIR NATURE, UNPREDICTABLE, THE USER SHALL BE RESPONSIBLE FOR THE PROPER SELECTION OF THE PRODUCT AND FOR THE PROPER USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



SPC TECHNOLOGY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	JC	DATE:	2/6/91
CHECKED BY:	JC	DATE:	11/21/91
APPROVED BY:	JL	DATE:	11/21/91

DRAWING TITLE:		Uninsulated Ring Terminals	
SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	TA-295	TA-295.dwg	C
SCALE:	NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1