

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

34803-0211

Status:

Active

Description:

CTX64 Female Terminal, D-Wind, Left Payoff, SAE 22



Series

image - Reference only

Documents:

- Drawing (PDF)

Product Specification PS-502306-001 (PDF)

Application Specification AS-502306-001 (PDF)

Application Specification AS-560065-001 (PDF)
- Application Specification AS-560065-001-FR (PDF)

RoHS Certificate of Compliance (PDF)

Product Literature (PDF)

General

Product Family	Crimp Terminals
Series	34803
Application	Signal
Crimp Quality Equipment	Yes
Product Literature Order No	987650-4561
Product Name	CTX64
UPC	884982186613

Physical

Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.114/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.10 to 1.65mm
Wire Size AWG	22
Wire Size mm²	0.22-0.35

Electrical

Current - Maximum per Contact	6A
Voltage - Maximum	14V DC

Material Info

Reference - Drawing Numbers

Application Specification	AS-502306-001, AS-560065-001, AS-560065-001-FR
Product Specification	PS-502306-001
Sales Drawing	SD-31301-053, SD-34803-001

EU RoHS

ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

34803Series

Use With

34729 2.54mm Pitch Stac64™ Right Angle Receptacle

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Description	Product #
Hand Crimp Tool for CTX64 Receptacle Terminal, 0.22, 0.30, 0.35mm² and 22 AWG	0638193700
FineAdjust™ Applicator for CTX64 Receptacle Terminals	0639010100

This document was generated on 12/04/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION