



**GREEN-LITE™ - 7.5" ROUND LED MAGNIFIER - 43" REACH  
- SCREW DOWN BASE**

**SKU# 62300-4**

*Equipped with next generation, surface mount LEDs, these innovative designs create the new standard for illuminated magnifiers. Your investment in new technology quickly pays for itself through energy savings. Made in the USA.*

**PRODUCT DESCRIPTION**

*Equipped with next generation, surface mount LEDs, these innovative designs create the new standard for illuminated magnifiers. Your investment in new technology quickly pays for itself through energy savings. Made in the USA.*

**Lighting Features**

- Highest lumen output in a lighted magnifier
- Reduced glare, heat and energy consumption
- Multi-angle LEDs for shadowless lighting at a full range of focal lengths and heights
- User controlled LED groups shine desired level of light exactly where required
- Superb dimming software via convenient, reliable membrane switch

**Optical Features**

- Precision ground, optical grade glass
- Largest lenses in the industry
- Standard 4 diopter (2x) lens – O.C. White exclusive
- Optional 5 diopter (2.25x) lens available

**Electrical Features**

- Low voltage (15-24v) power supplies are auto-switchable with worldwide approvals
- Plug in around the world by simply switching the end power cord
- Energy Star compliant (each unit uses 8 watts maximum)
- Auto shut off at 4 hour intervals to prevent energy waste while users are away

**Mechanical Features**

- High quality die cast aluminum shades and all steel arm components for ESD safety
- Patented "Elite" arms are slim but have the greatest holding power of any arm of this type in the world
- Virtually "maintenance zero"

SPECIFICATIONS

<b>Name</b>	Green-Lite™ - 7.5" Round LED Magnifier - 43" Reach - Screw Down Base
<b>SKU</b>	62300-4
<b>Product Line</b>	Green-Lite™
<b>Magnification</b>	2x (4 Diop)   2.25x (5 Diop) Optional
<b>Reach</b>	43"
<b>Mounting Style</b>	Screw Down Base
<b>Voltage</b>	120 Volt - 240 Volt
<b>ESD Safe</b>	Yes