



Magnilite® - Vision-Lite® Rectangular Magnifier - 43" Reach - Table Edge Clamp

SKU# 72400

Vision-Lite® Rectangular Magnifier with either a 3 Diopter (1.75X) or 4 Diopter (2X) lens. Features your choice of 25" or 43" Arm Reach with a Table Edge Base Assembly. **NEW** Glare Free "**FULL SPECTRUM**" "Bulb for high light output. **ESD Safe**.

PRODUCT DESCRIPTION

Vision-Lite® Fully Dimmable Magnifier

The largest and clearest magnifier on the market features excellent image clarity, lighting control and energy efficiency. Made in the USA.

Our original Green-Lite®! The Vision-Lite® is the world's first and only dimmable fluorescent illuminated magnifier. "Patented" state-of-the-art microchip controlled ballast technology allows the Vision-Lite® to be dimmable from 100% down to 25%, so that highly reflective surfaces can easily be seen by dimming the units exclusive high output three-sided bulb

The Vision-Lite® is available in two arm lengths, this model with a Table Edge Clamp. ESD Safety and unrivaled warranties are but only a couple of the best attributes. You cannot find a stouter magnifier anywhere!

- Made in the USA
- ESD safe and RoHS compliant
- Patented dimming technology for precise output control from 100% to 25%
- Shadowless wrap-around T5 bulb for uniform lighting at any level
- Crown white optical grade glass for highest resolution images
- 3 Diopter standard, 4 Diopter (2x) optional
- Rugged all metal construction
- Table edge clamp and other mounting choices
- 10 Year Mechanical Warranty...best in the business
- Also Available in 230v

SPECIFICATIONS

Name	Magnilite® - Vision-Lite® Rectangular Magnifier - 43" Reach - Table Edge Clamp
SKU	72400
Product Line	Magnilite®
Magnification	1.75x (3 Diop) 2x (4 Diop) Optional
Reach	43"
Mounting Style	Table Edge Clamp
Voltage	120 Volt 230 Volt Optional
ESD Safe	Yes