

Weller
100 Watt, 120v, 122Å°F to 1022Å°F Digital Shop Air Hot Air Station



Product Details	
Catalog No.	WAD101
UPC Code	037103194367
Wattage	100 W
Desoldering Pencil(s)	HAP1
Temperature Range	122° F to 1022° F
Voltage	120 V/24 V
Supplied Tip(s)	0058727821
Air Flow Volume	1 l/min - 6 l/min
Pump Type	Compressed Air
Packaging	Industrial Box/Carton
Literature	550294.pdf
Tech. Spec.	Solder Safety Warnings.pdf
Low Res. Image	WAD101_100.jpg
High Res. Image	WAD101_300.jpg
Stock Item	Normal Stock Item

The Weller Advantage

- Features digital temperature control with easy to read LED display for fast and accurate temperature set of the hot air
- Programmable using the optional WCB1 control module. Allows for temperature lockout for process control, temperature setback and °F to °C conversion
- **Applications:** Rework and repair of SMT boards. Sensitive applications requiring non-contact hot air. Some ground planes and multi-layer boards.

Package Details (Dimensions)

Product Features:

- WAD101 includes: HAP1 hot air pencil, PH60 stand and sponge
- Air flow is adjustable using knob on the side of the power unit
- Compact design, ideal for soldering, desoldering, rework SMT components
- Uses fast acting shop air or compressed nitrogen
- Air flow is actuated by a finger switch on the hot air pencil
- Full range of hot air nozzles is available
- ESD safe to protect sensitive components