

SCERX22ABA

Time Delay Relays

Not EU RoHS or ELV Compliant



Product Highlights:

- **SCE Specification Grade True Off-Delay Timing Series**
- **Input Voltage = 120 VAC**
- **Input Voltage = 125 VDC**
- **Contact - Arrangement = 2 Form C, DPDT, 2 C/O**
- **Contact Rating = 5A Resistive @ 120/240 VAC**

Mechanical Attachment:

- **Mounting Options = Socket**

Electrical Characteristics:

- **Input Voltage (VAC) = 120**
- **Input Voltage (VDC) = 125**
- **Contact Rating = 5A Resistive @ 120/240 VAC**

Termination Features:

- **Termination Type = 8-Pin Octal Style Plug**

Dimensions:

- **Approx. Dimensions (L x W x H) (mm [in]) = 50.00 x 50.00 x 83.00 [1.970 x 1.970 x 3.270]**

Contact Features:

- Delay Time = 0.5 seconds to 15 seconds
- Type of Control = Knob
- Repeatability, Max. = $\pm 1\%$

Configuration Features:

- [Contact - Arrangement](#) = 2 Form C, DPDT, 2 C/O
- Multiple Timing Ranges = Without

Industry Standards:

- Approved Standards = CE Approved, CSA Certified, UL Recognized
- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not suitable for lead free processing

Conditions for Usage:

- Temperature Range ($^{\circ}\text{C}$) = -30 – +65

Operation/Application:

- Mode of Operation = True Off-Delay

Other:

- [Series](#) = SCE Specification Grade True Off-Delay Timing
- Brand = Agastat