

# SURFACE MOUNT DISPLAY

ATTENTION **OBSERVE PRECAUTIONS** FOR HANDLING ELECTROSTATIC DISCHARGE SENSITIVE DEVICES

Part Number: KCSA02-136

## **Features**

- 0.2inch digit height.
- Low current operation.
- Excellent character appearance.
- Mechanically rugged.
- Gray face, white segment.
- Package: 650pcs / reel.
- Moisture sensitivity level : level 2a.
- RoHS compliant.

## Description

The Blue source color devices are made with InGaN on SiC Light Emitting Diode.


Static electricity and surge damage the LEDS.

It is recommended to use a wrist band or anti-electrostatic glove when handling the LEDs.

Blue

All devices, equipment and machinery must be electrically grounded.

# Package Dimensions& Internal Circuit Diagram





- 1. All dimensions are in millimeters (inches), Tolerance is ±0.25(0.01")unless otherwise noted.
- The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.
   The gap between the reflector and PCB shall not exceed 0.25mm.

SPEC NO: DSAG5799 **REV NO: V.5B** DATE: MAY/04/2013 PAGE: 1 OF 5 APPROVED: WYNEC **CHECKED:** Joe Lee DRAWN: Q.M.Chen ERP: 1351000416

# **Selection Guide**

Part No.	Dice	Lens Type	lv (ucd) [1] @ 10mA		Description
			Min.	Тур.	
KCSA02-136	Blue (InGaN)	White Diffused	2200	4300	Common Anode, Rt. Hand Decimal.

### Note:

- Luminous intensity/ luminous Flux: +/-15%.
   Luminous intensity value is traceable to the CIE127-2007 compliant national standards.

# Electrical / Optical Characteristics at TA=25°C

•								
Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions		
λpeak	Peak Wavelength	Blue	468		nm	IF=20mA		
λD [1]	Dominant Wavelength	Blue	465		nm	IF=20mA		
Δλ1/2	Spectral Line Half-width	Blue	21		nm	IF=20mA		
С	Capacitance	Blue	100		pF	VF=0V;f=1MHz		
VF [2]	Forward Voltage	Blue	3.2	4.0	V	IF=20mA		
lr	Reverse Current	Blue		10	uA	V <sub>R</sub> =5V		

## Notes:


- 1.Wavelength: +/-1nm. 2. Forward Voltage: +/-0.1V.
- 3. Wavelength value is traceable to the CIE127-2007 compliant national standards.

# Absolute Maximum Ratings at TA=25°C

Parameter	Blue	Units	
Power dissipation	120	mW	
DC Forward Current	30	mA	
Peak Forward Current [1]	100	mA	
Reverse Voltage	5	V	
Operating / Storage Temperature	-40°C To +85°C		

1. 1/10 Duty Cycle, 0.1ms Pulse Width.


SPEC NO: DSAG5799 **REV NO: V.5B** DATE: MAY/04/2013 PAGE: 2 OF 5 APPROVED: WYNEC **CHECKED:** Joe Lee DRAWN: Q.M.Chen ERP: 1351000416





RELATIVE INTENSITY Vs. WAVELENGTH


Blue

# KCSA02-136










# CIRCUIT DESIGN NOTES


- 1.Protective current—limiting resistors may be necessary to operate the Displays.
- 2.LEDs mounted in parallel should each be placed in series with its own current—limiting resistor.



SPEC NO: DSAG5799 APPROVED: WYNEC REV NO: V.5B CHECKED: Joe Lee DATE: MAY/04/2013 DRAWN: Q.M.Chen PAGE: 3 OF 5 ERP: 1351000416

# KCSA02-136

Reflow Soldering Profile For Lead-free SMT Process.




- NOTES:

  1.We recommend the reflow temperature 245°C(+/-5°C). The maximum soldering temperature should be limited to 260°C. 2.Don't cause stress to the epoxy resin while it is exposed to high temperature.
   3.Number of reflow process shall be 2 times or less.


# **Recommended Soldering Pattern** (Units: mm; Tolerance: ± 0.15)

# 1.44X4=5.76 10

# **Reel Dimension**




**Tape Specifications** (Units: mm)



SPEC NO: DSAG5799 APPROVED: WYNEC

**REV NO: V.5B CHECKED:** Joe Lee DATE: MAY/04/2013 DRAWN: Q.M.Chen

PAGE: 4 OF 5 ERP: 1351000416



 SPEC NO: DSAG5799
 REV NO: V.5B
 DATE: MAY/04/2013
 PAGE: 5 OF 5

 APPROVED: WYNEC
 CHECKED: Joe Lee
 DRAWN: Q.M.Chen
 ERP: 1351000416