

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [70929-2000](#)
Status: **Active**
Overview: [LFH™](#)
Description: 1.27mm Pitch LFH™ Matrix 50 Plug Cable Kit, Subassembly, 60 Circuits, Bright Tin (Sn) Front Shell Plating

Documents:

3D Model	Application Specification AS-70929-001 (PDF)
Drawing (PDF)	Application Specification AS-71624-001 (PDF)
Product Specification PS-70928 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General


Product Family	I/O Connectors
Series	70929
Application	Wire-to-Board
Comments	I/O Plug Connector Subassembly Use Tool 622001500 for inserting sticks into subassembly 70984 Terminal Sticks Supplied Separately
Component Type	I/O Plug Connector Subassembly
MolexKits	Yes
Overview	LFH™
Product Name	LFH™
Type	N/A

Physical

Circuits (Loaded)	60
Circuits (maximum)	60
Color - Resin	Black
Flammability	94V-0
Lock to Mating Part	None
Material - Metal	Aluminum
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Orientation	Vertical
PCB Retention	N/A
Packaging Type	Tray
Panel Mount	Yes
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-20°C to +80°C
Termination Interface: Style	N/A
Wire Size AWG	28, 30, 32, 34, 36

Electrical

Current - Maximum per Contact	1A
Shielded	Yes
Voltage - Maximum	40V



EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[70929Series](#)

Mates With

[70928 LFH™ Receptacle](#)

Solder Process Data

Duration at Max. Process Temperature (seconds)	40
Lead-free Process Capability	Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	3
Process Temperature max. C	245

Material Info**Reference - Drawing Numbers**

Application Specification	AS-70929-001, AS-71624-001
Product Specification	PS-70928, RPS-70928-002
Sales Drawing	SDA-70929-20**

This document was generated on 05/09/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION