

Capacitor, Tantalum, SMD, MnO2, Molded, 6.8 uF, 3216, +/-20% Tol, 20V@85C



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	3.2	+/-0.2
W	1.6	+/-0.2
H	1.6	+/-0.2
F	1.2	+/-0.1
S	0.8	+/-0.3
B	0.4	+/-0.15
X	0.1	+/-0.1
P	0.4	REF
R	0.4	REF
T	0.13	REF
A	1.4	MIN
G	1.1	REF
E	1.3	REF

Notes:

-In polarity stripe, at KEMET's option, type may be indicated:
 no symbol = Standard (or low leakage) MnO2 tantalum chip, O = LowESR T494, R = Low ESR T495, F = Fused T496, HT = 150C rated T498 (or B45196P, B45198P), H = 175C rated T499, M = Multiple anode construction T510 (and B45396R), KO = Organic cathode T520 or T521, KT = High temp organic cathode T525, KM = Multiple anode organic cathode T530, FD= Organic cathode face down terminals T528.

General Information	
Supplier:	KEMET
Part Type Description:	SMD, MnO2, Molded
Construction:	Standard Chip-MnO2

Specifications	
Capacitance:	6.8 uF
Voltage DC @ 85C:	20V
Voltage DC @ 105C:	16.7V
Voltage DC @ 125C:	13.4V
Tolerance:	+/-20%
Application:	General Purpose
Temperature Range:	-55/+125C
Body Type:	Molded Chip
ESR:	6 Ohm
Footprint:	3216
Termination:	Tin
RoHS:	Yes
Leakage Current:	1.4 uA
Dissipation Factor:	8%
Ripple @ 25C:	0.112 A
Ripple @ 85C:	0.101 A
Ripple @ 105C:	0.073 A
Ripple @ 125C:	0.045 A

Packaging Specifications	
Package Kind:	T&R
Package Size:	7in
Package Quantity:	2000