

9007CT62

9007C limit switch base - standard - for 2 NO/NC - 1/2" NPT entry



Main

Range of product	9007
Series name	Heavy duty
Product or component type	Limit switch base
Device short name	9007C
Body type	Standard plug-in
Product compatibility	9007C
Electrical connection	Screw-clamp terminals (12...22 AWG), 1...2
Cable entry	1 entry for 1/2" - 14 NPT conforming to ANSI B1.20.1
Ambient air temperature for operation	-20...185 °F for standard environment
Environmental characteristic	Standard environment
Sale per indivisible quantity	1

Complementary

Associated head	9007C
Associated connection component	9007CO62 9007CO66 9007CO68
Body material	Zinc
Function available	-
Mechanical durability	10000000 cycles
Width	1.55 in
Height	3.14 in
Depth	0.9 in
Product weight	0.48 kg
CAD overall width	1.55 in
CAD overall height	3.14 in
CAD overall depth	0.9 in

Environment

Shock resistance	60 gn (duration = 9 ms) conforming to IEC 60068-2-27
Vibration resistance	25 gn (f = 10...150 Hz) conforming to IEC 60068-2-6
NEMA degree of protection	NEMA 1 conforming to Nema type 250 NEMA 2 conforming to Nema type 250 NEMA 4 conforming to Nema type 250 NEMA 6 conforming to Nema type 250 NEMA 6P conforming to Nema type 250 NEMA 12 conforming to Nema type 250 NEMA 13 conforming to Nema type 250
IP degree of protection	IP67 conforming to IEC 60529
Class of protection against electric shock	Class 0 conforming to IEC 61140
Ambient air temperature for storage	-20...185 °F
Protective treatment	Epoxy powder coat

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Will be Compliant on 3Q2014 Will be Compliant on 3Q2014
Product environmental profile	Available

