

XCB4 Multi-Conductor - B-Plus Cross-Connect Wire



For more Information
please call

1-800-Belden1



General Description:

CAT5 (100MHz), 4-Pair, U/UTP-Unshielded, Premise Cross-Connect Cable, 24 AWG solid bare copper conductors, PVC insulation

Usage (Overall)

Suitable Applications: Cross-Connect, Interconnect

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
4	24	Solid	BC - Bare Copper

Total Number of Conductors: 8

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
PVC - Polyvinyl Chloride	0.914

Overall Cable

Overall Nominal Diameter: 3.531 mm

Pair

Pair Color Code Chart:

Number	Color
1	blue & White/blue
1	orange & white/orange
1	green & white/green
1	brown & white/brown

Mechanical Characteristics (Overall)

UL Temperature Rating: 60°C

Bulk Cable Weight: 28.276 Kg/Km

Min. Bend Radius/Minor Axis: 25.400 mm

Min. Bend/Installation: 35.560 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: UL444

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 08/19/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

XCB4 Multi-Conductor - B-Plus Cross-Connect Wire

Mil Order #39 (China RoHS):	Yes
Other Specification:	Meets Category 5 NEXT performance requirements as specified by TIA/EIA 568 B-2

Flame Test

UL Flame Test:	UL1685 UL Loading
-----------------------	-------------------

Plenum/Non-Plenum

Plenum (Y/N):	No
----------------------	----

Reference (Overall)

Previous Part Number:	22208270. 22208271
------------------------------	--------------------

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
XCB4 000K500	152 MT	5.897 KG	NONE		CAT5 4PR X-CONN KOC
XCB4 0001000	305 MT	7.258 KG	NONE		CAT5 4PR X-CONN REEL

Revision Number: 1 Revision Date: 08-14-2013

© 2013 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.