

W-Series
WSI 4/LD 60-150V AC/DC**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

The fuse terminals of the Weidmüller W Series are available in two different forms:

- Fuse terminal with pivoting retaining lever
- Fuse terminal with plug-in SIHA fuse holder

General ordering data

Type	WSI 4/LD 60-150V AC/DC
Order No.	1886570000
Version	W-Series, Fuse terminal, Rated cross-section: 4 mm ² , Screw connection
GTIN (EAN)	4032248492053
Qty.	50 pc(s).

**W-Series
WSI 4/LD 60-150V AC/DC**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Dimensions and weights

Length	50.7 mm	Width	9.1 mm
Height	42.5 mm	Height of lowest version	46 mm
Net weight	10.9 g		

Temperatures

Operating temperature		Storage temperature	
Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	120 °C

Additional technical data

Number of similar terminals	1	Type of mounting	Snap-on
Version	Screw connection, Fuse isolator, with LED, closed		

CSA ratings data

Certificate No. (CSA)	200039-1575489	Wire cross section max. (CSA)	12 AWG
Wire cross section min. (CSA)	30 AWG		

Clampable wires (rated connection)

Type of connection	Screw connection	Stripping length	8 mm
Blade size	0.6 x 3.5 mm	Connection direction	on side
Number of connections	2	Clamping range, rated connection, min.	0.5 mm ²
Clamping range, rated connection, max.	6 mm ²	Clamping screw	M 3
Tightening torque, min.	0.5 Nm	Tightening torque, max.	0.8 Nm
Torque level with DMS electric screwdriver	2	Gauge to IEC 60947-1	A3
Wire connection cross section, solid core, max. rated connection	0.5 mm ²	Wire connection cross section, solid core max. rated connection	4 mm ²
Wire connection cross section, stranded, rated connection, min.	1.5 mm ²	Wire connection cross section, stranded, rated connection, max.	4 mm ²
Wire connection cross section, finely stranded, max.	4 mm ²	Wire connection cross-section, finely stranded, min.	0.5 mm ²
Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, min.	0.5 mm ²	Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, max.	2.5 mm ²
Wire connection cross section AWG, min.	AWG 22	Wire connection cross section AWG, max.	AWG 12

Dimensions

TS 35 offset	25 mm
--------------	-------

Rated data

Rated cross-section	4 mm ²	Rated voltage to adjoining terminal	500 V
Rated current	6.3 A	Current at maximum wires	6.3 A
Standards	IEC 60947-7-3		

Data sheet

W-Series WSI 4/LD 60-150V AC/DC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

UL ratings data

Certificate No. (cURus)	E60693VOL1SEC81	Conductor size Factory wiring max. (cURus)	12 AWG
Conductor size Factory wiring min. (cURus)	30 AWG	Conductor size Field wiring max. (cURus)	12 AWG
Conductor size Field wiring min. (cURus)	30 AWG		

Material data

Material	Wemid	Colour	Black
UL 94 flammability rating	V-0		

System specifications

Product family	W-Series	Type of connection	Screw connection
Connection direction	on side	Number of levels	1
Number of connections	2	No. of clamping points per level	2
Levels cross-connected internally	No	Mounting rail	TS 35
End cover plate required	No		

Display element

Operating voltage for display, max.	150 V	Operating voltage for display, min.	60 V
Type of voltage for indicator	AC/DC		

Fuse terminals

Cartridge fuse	G-Si. 5 x 20	Display	LED
Fuse holder (cartridge holder)	for screw fixing	Operating voltage, max.	150 V
Type of voltage for indicator	AC/DC		

Classifications

ETIM 3.0	EC000899	UNSPSC	30-21-18-11
eClass 5.1	27-14-11-16	eClass 6.2	27-14-11-16
eClass 7.1	27-14-11-16		

Approvals

Approvals



ROHS Conform

Data sheet

W-Series
WSI 4/LD 60-150V AC/DC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Drawings

