




This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.



Customer drawing

REVISIONS				
SYM	ECN	DESCRIPTION	DATE	APPROVED
1			12/11/07	

D-SUB TECHNICAL DATA

SHELL : Steel 2.5um(100u") min tin over 1.25um(50u") min nickel
BODY : Glass filled thermoplastic.
Flame retardant to UL94 V-0 Color Black
ELECTRICAL : Voltage rating 300 V RMS at 50 Hz
Withstanding Voltage >1000 V RMS at 50 Hz for one minute
Insulation resistance >5000 M Ohms
CLIMATIC : Temperature range -55 °C up to 155°C
Damp heat 56 days(40 °C-95% HR)
MARKING : Amphenol...(Series No.)
Commercial reference
Manufacturing date

PRODUCT CODE

L 77TW A 3W3 S

L: RoHS Compliance

77TW: tin plated shell

Shell Size :A

Contact type:
S:Female
P: Male

Configuration: 3W3

UNLESS OTHERWISE SPECIFIED TOLERANCES		APPROVAL		DATE	Amphenol
U.S. METRIC		DRAWN	Sunny.Li	12/11/07	
		CHECKED	tk.wang	12/11/07	
		CHECKED			
.X +/- 0.50					TITLE
.XX +/- 0.30					
.XXX +/- 0.20					
FRACTIONS +/-					
ANGLES +/- 5°		DRAWING FILE :			Hybrid connector, TW series
FOR MATERIALS AND FINISHES SEE NOTES		ANGLE OF PROJECTION			
REMOVE SHARP EDGES					
DIMENSIONS					
U.S. INCHES					
METRIC MM					
		SIZE		DRAWING NO.	REV.
		A4		C L77TWA3W3S	1
		SCALE		NONE	SHEET 1 OF 1