







REV.	DESCRIPTION	DATE	APPROVED
1	Modified as per ECN No. 0627	11/11/05	HV
2	Modified as per ECN No. 0668 & 0673	7/18/08	HV



This document is the property of REGAL BELOIT CORPORATION ("RBC") including its subsidiaries and divisions. It contains proprietary information of RBC. This information must not be exported outside the United States, nor the information contained therein shall be disclosed to others without the express written consent of RBC, and that the information shall be used by the recipient only as approved expressly by RBC. This document shall be returned to RBC upon its request. This document may be subject to certain restrictions under U.S. export control laws and regulations.



SPECIFICATIONS :

"GEM-III Capacitors are manufactured with High Grade Metallized Polypropylene Film"

Main Capacitance	: 15.00 μ F $\pm$ 6%
Secondary Capacitance	: NIL
Volts	:370AC
Leakage Current	:30 μ A Max.
Frequency	:50/60 HZ
Operating Temperature	: -40 DEG C TO 70 DEG C
Storage Temperature	: -40 DEG C TO 90 DEG C
Operative Life	:60,000 HRS WITH 94% SURVIVAL
Dissipation Factor	:0.1% MAX.
Case Material	:ALUMINIUM
Cover Material	:STEEL TIN PLATED
Terminals	: 0.250"x0.031" Quick Connect Blades
Dielectric Fluid	:DIELEKTROL VI
Internal Protection	: UL RECOGNIZED PSI A10000AFC

FOR ADDITIONAL INFO REFER TO:	SIGNATURES		DATE
APPLIED PRACTICES	MODEL	NPS	07/25/08
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES	DETAIL	NPS	07/25/08
TOLERANCE ON:	CHECKED	HV	07/25/08
1 PL DECIMALS $\pm$ 0.1	ENGRG	-	-
2 PL DECIMALS $\pm$ 0.01	MFG	-	-
3 PL DECIMALS $\pm$ 0.001	QUALITY	-	-
ANGLES $\pm$ 0.5	ISSUED	-	-
FRACTIONS $\pm$			
FINISH ✓			
MATERIAL	SOLID MODEL: 2TCAPACITOR_ASM		



REGAL-BELOIT CORPORATION

GEM III CAPACITOR OUTLINE DRAWING

REF. No: .

SHEET 1 OF 1