


Spec Sheet

SMD Power Inductors for Industrial / Automotive Comfort and Safety Applications (NR series H type / V type / S type)

NRS8030T220MJGV



■ Features

- Item Summary
22 μ H($\pm 20\%$), 1750mA, 1900mA
- Lifecycle Stage
Mass Production
- AEC-Q200 qualified
- Standard packaging quantity (minimum)
Taping 1000pcs

■ Products characteristics table


CaseSize (EIA/JIS)	~/8030
Inductance	22 μ H($\pm 20\%$)
Inductance Measuring Frequency	100kHz
Rated Current -Saturation Current	1750mA
Rated Current -Temperature Rise Current	1900mA
DC Resistance (max)	0.091 Ω
Avg. of DC.Resistance	0.07 Ω
Temperature Range	-40°C to 125°C
Self-resonant Frequency (min)	16MHz
RoHS Compliance	Yes
Halogen Free	Yes
Soldering Method	Reflow

■ External Dimensions

L	8mm ± 0.2
W	8mm ± 0.2
H	3mm max

■ Recommended Land Patterns

【推奨ランドパターン】 実装上の注意 ・実装状態を確認の上ご使用ください。また、本製品ははんだ付はリフローはんだ工法に限り、手付けはんだ工法は不可です。
【Recommended Land Patterns】 Surface Mounting ・Mounting and soldering conditions should be checked beforehand. ・Applicable soldering process to these products is reflow soldering only.



SMD Power Inductors (NR series/NR series H type/S type /V type)			
Type	A	B	C
NRS8030,	1.8	5.6	7.5
NR 6040, NRS6040			

unit:mm

2014.01.23

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.
TAIYO YUDEN reserves the right to make change to the Date at any time without notice.
Before making final selection, please check product specification.